

PIT en1.1a-5m-s

401112



Technical details

Approvals:	CE
Attachment:	Magnetic clamp
Mounting position:	Any
Number of N/O:	2
Max. current at DC13 I (6 cycles/min):	0.7 A
Voltage at DC13:	30 V
Max. current at DC12:	1.0 A
Voltage at DC12:	30 V
Protection type, housing:	IP65
Diameter:	45.0 mm
Width dimension:	45.0 mm
Height dimension:	125.0 mm
Depth dimension:	45.0 mm
Gross weight:	493 g
Net weight:	470 g
Ambient temperature:	0 - 50 °C