

Universe	Professional
Type	Lighting
Category	Compact rugged headlamps
Subcategory	Compact rugged headlamps



PIXA® 3

The PIXA 3 headlamp is rugged and versatile. The multi-beam adapts to all situations: close-range work, movement, and long-range vision. CONSTANT LIGHTING technology: brightness does not decrease gradually as the batteries are drained. Depending on the need, it may be worn on the head, mounted on the helmet, or placed on the ground.



Multi-beam: multiple lighting modes available for close-range work, for movement or for long-range vision.



Knob can be manipulated with gloves on to facilitate use of the headlamp under any conditions.

Short Description

Multi-beam headlamp suitable for proximity lighting, movement and long-range vision, with CONSTANT LIGHTING technology. 100 lumens max

Selling Points

- Headlamp keeps hands free for work and can be worn:
 - on the head with the headband
 - attached to the helmet with a mounting plate (included)
 - placed on the ground
- CONSTANT LIGHTING technology ensures brightness that does not gradually decrease as the battery drains
- Several lighting modes adapt to each situation:
 - a mode adapted for close range work: wide, uniform beam
 - a mode adapted for movement: mixed beam with focused component allows user to move around comfortably
 - a mode adapted for long-range vision: focused beam
- Lighting for professionals that is reliable, practical and durable:
 - automatically switches to reserve mode when batteries are almost drained (signaled by blinking light and red indicator)
 - knob is easy to use, even with gloves on
 - storage position helps protect the headlamp lens and prevents inadvertently turning it on
 - may be used in explosive atmospheres (ATEX: Zone 2/22)
 - excellent resistance to falls (2 m), impacts, and crushing (80 kg)
 - comfortable and washable elastic headband
 - resistant to chemicals (see www.petzl.com/PIXA)

Specification

- Weight: 160g
 - Technology: CONSTANT LIGHTING
 - Beam pattern: wide, mixed, focused
 - Energy: 2 AA/LR06 batteries (included)
 - Battery compatibility: rechargeable Ni-MH and lithium
 - Certification(s): CE, ATEX : Zone 2/22, ANSI/NEMA FL1
 - Watertightness: IP 67 (waterproof to -1 meter for 30 minutes, no maintenance required after immersion)
-

Lighting performance

	Brightness	Distance	Burn time	Reserve brightness	Reserve distance	Reserve burn time	Total battery life
Lighting technology	Lighting modes	Petzl lighting performance					
CONSTANT LIGHTING	Mode 1 (wide)	20 lm	15 m	26 h	10 lm	10 m	39 h
	Mode 2 (mixed)	60 lm	45 m	6h30		20 m	13 h
	Mode 3 (focused)	100 lm	90 m	3h30	16h30		

Specifications by reference

Reference(s)	E78CHB 2
Color(s)	black/yellow
Made in	MY
Guarantee	3 years
Packing	1
Case quantity	36
EAN	3342540098497

Accessory(ies) POCHE PIXA
 RUBBER
 PIXA headband

Related product(s) VERTEX® BEST
 ALVEO VENT