

# LED enclosure light - PLD E 608 W 265 - 2702224

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



LED enclosure light, AC wide-range input, color temperature 4000 K, with motion sensor

## Product Description


The LED light is designed to illuminate the interior of control cabinets. The integrated optics ensure optimum illumination of the control cabinet. Tool-free assembly using the integrated retaining hook system. This allows several lights to be successively switched. Switching the light on and off takes place via an integrated motion sensor.

## Why buy this product

- Tool-free mounting, thanks to the patented snap-in hook system
- Worldwide use, thanks to AC wide range input
- Integrated motion detector saves on MRP and installation costs for door position switches
- Series connection reduces cabling effort for control cabinets arranged in series
- Optimum lighting of the control cabinet, thanks to integrated optics
- LED service life of 50,000 h (L70 value) prevents bulb replacement



## Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 057095
GTIN	4055626057095
Custom tariff number	94054039

## Technical data

### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

### Dimensions

Width	91 mm
Height	44 mm
Length	265 mm

# LED enclosure light - PLD E 608 W 265 - 2702224

## Technical data

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 %
Permissible humidity (storage/transport)	5 % ... 95 %
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Degree of protection	IP20

### General

Socket	none
Housing material	Plastic
Assembly instructions	Magnet attachment available as an accessory Screw fixings available as accessories
Net weight	761.8 g
Mounting type	Snap-in hook system

### Power supply for module electronics

Connection method	Installation coupler
	Installation coupler
Number of positions	3
Supply voltage range	85 V AC ... 265 V AC (50/60 Hz) 100 V AC ... 250 V AC (50/60 Hz, nominal voltage)
Power consumption	9.8 W

### Light properties

Source of light type	LED
Number of LEDs	23
Service life, lighting appliance	50,000 h (L70)
Light color	Neutral white
Color temperature	4000 K
Color rendering index	85
Luminous flux	685 lm (Net luminous flux)
Illumination	max. 1255 lx (50 cm distance)

### Motion detector

Detection range	1.5 m ±0.25 m
Detection angle	35 ° ±5° (Horizontal and vertical)
Lighting duration	180 s (Retriggered)

### Standards and Regulations

Mechanical tests	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6 5g
	Shock in acc. with EN 60068-2-27/IEC 60068-2-27 25g, 11 ms period, half-sine shock pulse
	Continuous shock according to EN 60068-2-27/IEC 60068-2-27 10g

# LED enclosure light - PLD E 608 W 265 - 2702224

## Technical data

### Standards and Regulations


Protection class	I
------------------	---

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


## Drawings

Connection diagram




Connection of the supply voltage of a light

Connection diagram




Forwarding of the supply voltage with the series connection of lights

Dimensional drawing




Connection of a light

Dimensional drawing




Dimensional drawing for screw mounting

Schematic diagram



Schematic diagram



Series connection of two lights

## Approvals

### Approvals

# LED enclosure light - PLD E 608 W 265 - 2702224

## Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

## Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 255026
mm <sup>2</sup> /AWG/kcmil		30-14	

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 255026
mm <sup>2</sup> /AWG/kcmil		30-14	

EAC		RU *- DE.**08.B.01474
-----	--	--------------------------

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>
------------------	--	---

## Accessories

Accessories

Installation connector

Connector - PLD E 608-CO-MS - 2702308



Connector for series connection, black, 3-pos.

## LED enclosure light - PLD E 608 W 265 - 2702224

### Accessories

Connector - PLD E 608-CO-FS - 2702309



Socket for power supply and series connection, black, 3-pos.

---

### Mounting material

Mounting material - PLD E 608-ME MM - 2702315



Set for magnetic mounting of class 600 PLD enclosure lights

---

Mounting material - PLD E 608-ME SM - 2702316



Set for screw mounting of class 600 PLD enclosure lights, including screws

---

Mounting material - PLD E 608-ME SFM - 2702317



Set consisting of two mounting carriages with snap-in hooks for class 600 PLD enclosure lights (replacement part)

---

### Power cable

Power cable - PLD E 608-CA-3,0/FS AM - 2702302



Power cable, 3-position, PVC, orange RAL 2004, free cable end, on Socket straight, black, Cable length: 3 m

---

## LED enclosure light - PLD E 608 W 265 - 2702224

### Accessories

Power cable - PLD E 608-CA-3,0/FS/UL - 2702306



Power cable, 3-position, PVC, gray RAL 7001, free cable end, on Socket straight, black, Cable length: 3 m, with UL approval

---

Power cable - PLD E 608-CA-MS/0,6/FS AM - 2702303



Power cable, 3-position, PVC, orange RAL 2004, Plug straight, black, on Socket straight, black, Cable length: 0.6 m

---

Power cable - PLD E 608-CA-MS/0,6/FS/UL - 2702307



Power cable, 3-position, PVC, gray RAL 7001, Plug straight, black, on Socket straight, black, Cable length: 0.6 m, with UL approval

---

Power cable - PLD E 608-CA-MS/1,0/FS AM - 2702304



Power cable, 3-position, PVC, orange RAL 2004, Plug straight, black, on Socket straight, black, Cable length: 1 m

---

Power cable - PLD E 608-CA-MS/4,0/FS AM - 2702305



Power cable, 3-position, PVC, orange RAL 2004, Plug straight, black, on Socket straight, black, Cable length: 4 m

---

Power distributor

## LED enclosure light - PLD E 608 W 265 - 2702224

### Accessories

T distributor - PLD E 608-CO-MS/FS/FR - 2702310



T-distributor with 2 sockets and one connector for series connection, black, 3-pos.

---

---

Phoenix Contact 2017 © - all rights reserved  
<http://www.phoenixcontact.com>