

1 Port USB Wireless N Network Print Server with 10/100 Mbps Ethernet Port - 802.11 b/g/n

Product ID: PM1115UWEU



The PM1115UWEU Wireless-N Print Server lets you share a standard USB printer with multiple users simultaneously over a WiFi network, or a wired LAN connection.

This compact wireless print server supports 802.11b/g/n wireless standards for functionality with almost any wireless network, plus, serving as a primary or backup interface the print server also offers an RJ45 port for 10/100 Mbps wired connections. Providing wireless network printing access enables you to place your printer in any location with network access and avoids the added cost of purchasing individual printers for each workstation or area.

This wireless USB print server can have you up and running in minutes, using either a web-based interface or a Windows based installation wizard, and also features a WiFi Protected Setup (WPS) button for quick and easy connection to your wireless network. Compatibility with USB 2.0 standards and a wide variety of USB printers and operating systems makes this network print server perfect for installation into mixed environments, with Simple Network Management Protocol (SNMP) support for remote monitoring.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Convert a standard USB printer into a standalone, wireless printer and share between multiple networked computers
- A convenient network printing solution for education and government institutions
- Eliminate the performance issues of an always-on, dedicated PC acting as the printer server



Features

- Compliant with 802.11b/g/n wireless networks, with data rates up to 150 Mbps
- USB 2.0 support
- Optional 10/100 Mbps RJ-45 LAN Port
- Compact, lightweight design with an internal antenna
- Supports SNMP for remote printer management works with most SNMP based applications
- Easy-to-use web interface or Windows-based configuration and setup
- · Built-in multi-function button for resetting the device, loading factory defaults or printing a self-test page
- Built-in WPS (WiFi Protected Setup) button for simple connection to a wireless network
- Supports DHCP Server/Client protocols, and UPnP

н	2	r	М	1A	12	re

Warranty 2 Years

Ports

Interface USB 2.0

RJ45 (10/100 Ethernet)

Wireless Ethernet

Industry Standards IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-T, IEEE

802.11b/g/n Wireless

Performance

Compatible Networks 10/100 Mbps

Frequency 2.4 GHz

Security Features WEP Data Encryption

WPA and WPA2-PSK Data Encryption

Supported Protocols TCP/IP (LDP / LPR Printer Port)

IPX

NetBEUI

AppleTalk



SNMP

SMB over IP

Connector(s)

USB Type-A (4 pin) USB 2.0 Connector Type(s)

RJ-45

Wireless N (IEEE 802.11n)

Software

OS Compatibility Windows XP, Vista, 7, 8, 8.1, 10, 11

Windows Server 2003, 2008 R2, 2012, 2016, 2019

Mac OS 10.x, 9.x

Linux 2.4.x to 4.4.x <i>LTS Versions only</i>

Special Notes / Requirements

System and Cable

Requirements

USB printer cable not included

Note

OS Compatibility refers to the included software only - the Print

Server itself can be used without software on any platform that

supports network printing

Indicators

LED Indicators

USB

Status

WLAN

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 500 mA

5 DC **Output Voltage**

Output Current 2 A

Center Tip Polarity Positive



Plug Type C

Power Consumption (In

Watts)

10

Environmental

Operating Temperature 0C to 50C (32F to 122F)

Storage Temperature -5C to 65C (23F to 149F)

Humidity 0~70% RH (Non-Condensing)

Physical Characteristics

Color White

Material Plastic

Product Length 2.8 in [72 mm]

Product Width 2.3 in [58 mm]

Product Height 1.0 in [25 mm]

Weight of Product 2.3 oz [65 g]

Packaging Information

Package Length 9.1 in [23 cm]

Package Width 5.9 in [15.1 cm]

Package Height 2.8 in [70 mm]

Shipping (Package)

Weight

11.3 oz [319 g]

What's in the Box

Included in Package Wireless Print Server

Power Adapter

Software CD

Quick Install Guide

^{*}Product appearance and specifications are subject to change without notice.