

# PME1WU2B-GR

Basic Protection Against Power Surges for Computers and Electronics

Includes: User Manual



## Technical Specifications

### Output

Number of Outlets	1.0
Receptacle Style	CEE 7 Schuko

### Input

Nominal Input Voltage	220V, 230V, 240V
Input frequency	50/60 Hz
Input Connections	Schuko CEE 7/7P
Input Power	4000.0Watts
Maximum Input Current	16.0A

### Surge Protection and Filtering

Surge energy rating	680Joules
ts_nm_surge_response	1ns
Peak Current Normal Mode	15kAmps

### Physical

Maximum Height	93MM, 9.32CM
Maximum Width	63MM, 6.31CM
Maximum Depth	40MM, 4.0CM
Net Weight	0.13KG
Shipping weight	0.17KG
Shipping Height	100MM, 10.0CM
Shipping Width	90MM, 9.0CM
Shipping Depth	68MM, 6.8CM
Color	Black
Master Carton Dimensions (Length x Width x Height)	290 x 288 x 128MM
Master Carton Units	12.0
Master Carton Weight	2.35
Units per Pallet	1008.0
SCC Codes	1073130434701 6

### Environmental

Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000meters

### Conformance

Approvals	CE, CE Mark
-----------	-------------

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs

### SIGN UP FOR EMAIL

I'd like to receive news and commercial info from Schneider Electric and its affiliates via electronic communication means such as email. For more details, please read our Privacy Policy.



OK

### WHO WE ARE

- [About APC](#)
- [Investor Relations](#)
- [Careers](#)
- [Sustainability](#)

### CONNECT WITH US

- [Press](#)
- [APC Blog](#)
- [Schneider Electric Data Centre Blog](#)
- [Contact Us](#)

### FIND A RESELLER

 Find

### CATALOG KEYCODE

 Go


[Terms & Conditions](#)

[Data Privacy and Cookie Policy](#)

2020, APC by Schneider Electric