



PME5B-GR

Basic Protection Against Power Surges for Computers and Electronics

Includes: User Manual



Technical Specifications

Output

Number of Outlets	5.0
Receptacle Style	CEE 7 Schuko

Input

Nominal Input Voltage	220V, 230V, 240V
Input frequency	50/60 Hz
Input Connections	Schuko CEE 7/7P
Cord Length	1.52meters
Number of Power Cords	1
Input Power	2300.0Watts

Surge Protection and Filtering

Surge energy rating	680Joules
ts_nm_surge_response	1ns
Peak Current Normal Mode	15kAmps

Physical

Maximum Height	40MM, 4.0CM
Maximum Width	304MM, 30.4CM
Maximum Depth	63MM, 6.3CM
Net Weight	0.47KG
Shipping weight	0.55KG
Shipping Height	334MM, 33.4CM
Shipping Width	118MM, 11.8CM
Shipping Depth	46MM, 4.6CM
Color	Black
Master Carton Dimensions (Length x Width x Height)	357 x 300 x 270MM
Master Carton Units	12.0
Master Carton Weight	7.27
Units per Pallet	324.0
SCC Codes	1073130434703 0

Environmental

Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000meters

Conformance

Approvals	CE, CE Mark
-----------	-------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs

SIGN UP FOR EMAIL

I'd like to receive news and commercial info from Schneider Electric and its affiliates via electronic communication means such as email. For more details, please read our Privacy Policy.

OK

WHO WE ARE

[About APC](#)
[Investor Relations](#)
[Careers](#)
[Sustainability](#)

CONNECT WITH US

[Press](#)
[APC Blog](#)
[Schneider Electric Data Centre Blog](#)
[Contact Us](#)

FIND A RESELLER

Find

CATALOG KEYCODE

Go



[Terms & Conditions](#)

[Data Privacy and Cookie Policy](#)

2020, APC by Schneider Electric