


PNOZ X3 110VAC 24VDC 3n/o 1n/c 1so

774314



Technical details

| | |
|--|--|
| Approvals: | CE;cULus Listed;TÜV;KOSHA;CCC |
| Application options: | Safety gate monitor;Instantaneous E-STOP monitoring;Limit switch |
| Operating modes: | Single-channel;Automatic reset;Dual-channel;Detection of shorts across contacts;Monitored manual reset |
| Product standard: | EN 60947-5-1 |
| Standards: | EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1 |
| Supply voltage (V): | 110,0 |
| Supply voltage type: | AC |
| Supply voltage type 2: | DC |
| Supply voltage 2 (V): | 24 |
| Terminal style: | fixed |
| Terminal type: | Screw terminal |
| Number of instantaneous safety contacts: | 3 |
| Number of auxiliary contacts: | 1 |
| Number of semiconductor outputs: | 1 |
| Stop category: | 0 |
| Max. current at DC13 I (6 cycles/min): | 6.0 A |
| Max. current at AC15: | 5.0 A |
| Width dimension: | 45.0 mm |
| Height dimension: | 87.0 mm |
| Depth dimension: | 121.0 mm |

| | |
|----------------------|-------------|
| Gross weight: | 385 g |
| Net weight: | 375 g |
| Ambient temperature: | -20 - 55 °C |