



Technical details

Approvals:	CE;cULus Listed;TÜV;KOSHA;CCC
Application options:	Safety gate monitor;Instantaneous E-STOP monitoring;Limit switch
Operating modes:	Single-channel;Automatic reset;Dual-channel;Detection of shorts across contacts;Monitored manual reset
Product standard:	EN 60947-5-1
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Supply voltage (V):	24,0
Supply voltage type:	AC
Supply voltage type 2:	DC
Supply voltage 2 (V):	24
Terminal style:	fixed
Terminal type:	Screw terminal
Number of instantaneous safety contacts:	3
Number of auxiliary contacts:	1
Number of semiconductor outputs:	1
Stop category:	0
Max. current at DC13 I (6 cycles/min):	6.0 A
Max. current at AC15:	5.0 A
Width dimension:	45.0 mm
Height dimension:	87.0 mm
Depth dimension:	121.0 mm

Gross weight:	385 g
Net weight:	375 g
Ambient temperature:	-20 - 55 °C