

Professional Soldering Tool

Cordless-Refillable Butane Gas Powered Soldering Tool Kit

Ultrasonically Welded gas tanks prevents gas leaking on exposure to impact, UV light or hot and cold temperatures. Butane compatible plastics. Medium Power adjustable from 10 - 60 watts.

- Fast, flint sparked ignition
- 60 minute run time
- Anti Static ESD Safe
- 7 assorted spare tips available
- Ready to melt solder in less than 40 seconds from ignition
- Flameless combustion (solder & hot air modes)
- Refills in less than 20 seconds with any standard butane lighter fuel
- Adjustable temperature control (equivalent to 10 60 watts)
- Ergonomic handle
- Safety cut off switch
- Max. Temperature 400 °C

Kit includes:

Soldering iron with 2.4mm soldering tip (MK2S)

Flame Tip (CX90)

Hot Blow Tip (CX81)

Hot Knife Tip (CX70)



MK2K-B

Professional Iron kit in blister



MK2S

Professional Soldering Iron with CX24 Tip



MK2K-C

Professional Iron kit in carton



CX10

Professional 1.0 mm - Oblique Tip







CX24 Professional 2.4 mm - Oblique Tip



Professional 3.2 mm - Oblique Tip



CX48 Professional 4.8 mm - Oblique Tip



CX70 Professional Hot Knife Tip



CX81 Professional Hot Blow Tip



CX90 Professional Flame Tip

