ACCESSORIES







COMPARTMENT STORAGE BOX PSK55000-PA02-4

- For safe marking of still-to-connect wires.
- 49-compartment storage box in impact-resistant plastic for convenient on-site combination marking.
- Perfect overview allows quick marking on mounting site.
- Transparent lid for visual confirmation of contents.
- Filled with PA02 markers and installation tools.

INFORMATION

Design

A compartment storage box with 49 removable compartments containing PA02 markers and installation tools.

The PA02 marker is a closed and adjustable marker sleeve for wires still not connected. Its unique profile with spring-action collars covers a wide diameter range.

Material

PA02: Soft PVC.

Characters

PA02: The characters are hot stamped for excellent readability and long-lasting durability.

Refills

Available from the standard Partex product range

Temperature range

PA02: Shape-resistant from -30 °C to +60 °C

PA02 durability

- Flame-proof @ UL94-V0 3 mm.
- Chemical resistance meeting Partex' testing program.
- Temperature and ageing resistance meeting Partex' testing program.

OVERVIEW

MARKER BOX CONTENTS

Product	Colour	Number/Product
A-Z	Yellow/Black	200
0-9	Yellow/Black	200
- /	Yellow/Black	200
GRD	Yellow-Green/Black	200
+	Red/White	200
-	Blue/White	200
Blank	-	200
L1, L2, L3	Yellow	100
N	Blue/White	200
Teflon-coated installation tool in stainless steel	-	2

А	в	с	D	E	F	G	н	I	J	
к	L	м	N	0	Ρ	Q	R	s	т	
U	v	w	x	Y	z	-	/	GRD	N	
0	1	2	3	4	5	6	7	8	3T	
9	L1	L2	L3	-	÷	BLANK	ЕМРТҮ	ЕМРТҮ	PAD3T	

Placement in PSK55000-PA02 compartment storage box.

PRODUCT SIZES


Marker Box	Length, mm	Width, mm	Height, mm
PSK55000-PA02-4	410	320	50

Marker	Diameter, mm	Area mm ²	Inch	AWG
PA-02	1.3-3.0	~0.2-1.5	.051"118"	22-16

Installation tool	Length, mm	Diameter, mm	Inner diameter, mm
PAD-3T	100	3,1	1,8

ACCESSORIES

PAD INSTALLATION TOOL



PAD-3T Teflon-coated fitting tool in stainless steel with axial hole at heavy end designed for wire fitting. PAD is designed for Partex PA02 and PA1 markers.

ORDERS

ORDERING INFORMATION AND PACKAGING

Article number	Description	Number/package
PA-02003AV40.A	PA YELLOW: A	200x5
PA-02003AV40.B	PA YELLOW: B	200x5
PA-02003AV40.C	PA YELLOW: C	200x5
PA-02003AV40.D	PA YELLOW: D	200x5
PA-02003AV40.E	PA YELLOW: E	200x5
PA-02003AV40.F	PA YELLOW: F	200x5
PA-02003AV40.G	PA YELLOW: G	200x5
PA-02003AV40.H	PA YELLOW: H	200x5
PA-02003AV40.I	PA YELLOW: I	200x5
PA-02003AV40.J	PA YELLOW: J	200x5
PA-02003AV40.K	PA YELLOW: K	200x5
PA-02003AV40.L	PA YELLOW: L	200x5
PA-02003AV40.M	PA YELLOW: M	200x5
PA-02003AV40.N	PA YELLOW: N	200x5
PA-02003AV40.0	PA YELLOW: O	200x5
PA-02003AV40.P	PA YELLOW: P	200x5
PA-02003AV40.Q	PA YELLOW: Q	200x5
PA-02003AV40.R	PA YELLOW: R	200x5
PA-02003AV40.S	PA YELLOW: S	200x5
PA-02003AV40.T	PA YELLOW: T	200x5
PA-02003AV40.U	PA YELLOW: U	200x5
PA-02003AV40.V	PA YELLOW: V	200x5
PA-02003AV40.W	PA YELLOW: W	200x5
PA-02003AV40.X	PA YELLOW: X	200x5
PA-02003AV40.Y	PA YELLOW: Y	200x5
PA-02003AV40.Z	PA YELLOW: Z	200x5
PA-02003AV40	PA YELLOW: -	200x5
PA-02003AV40./	PA YELLOW: /	200x5
PA-02003AV40.GRD	PA YELLOW-GREEN: GROUND	200x5
PA-02003AV69.N	PA BLUE: N	200x5
PA-02003AN4	PA UNMARKED YELLOW	200x5
PA-02003AV40.0	PA YELLOW: 0	200x5
PA-02003AV40.1	PA YELLOW: 1	200x5
PA-02003AV40.2	PA YELLOW: 2	200x5
PA-02003AV40.3	PA YELLOW: 3	200x5
PA-02003AV40.4	PA YELLOW: 4	200x5
PA-02003AV40.5	PA YELLOW: 5	200x5
PA-02003AV40.6	PA YELLOW: 6	200x5
PA-02003AV40.7	PA YELLOW: 7	200x5
PA-02003AV40.8	PA YELLOW: 8	200x5
PA-02003AV40.9	PA YELLOW: 9	200x5
PA-02006AV40.L1	PA YELLOW: L1	100x5
PA-02006AV40.L2	PA YELLOW: L2	100x5
PA-02006AV40.L3	PA YELLOW: L3	100x5
PA-02003AV69	PA BLUE: -	200x5
PA-02003AV29.+	PA RED:+	200x5
PAD-3T	PAD 3 TEFLON-COATED	1
	INSTALLATION TOOL	