

Product information  
 Manuf. part number PTP950NWZG1  
 Manufacturer Brother



## Brother P-Touch P950NW - Label printer

| Product information     |  |
|-------------------------|--|
| Manufacturer            | Brother  |
| Manuf. part number      | PTP950NWZG1  |
| Main specifications     |  |
| Product Description     | Brother P-Touch P950NW - label printer - monochrome - thermal transfer   |
| Printer Type            | Label printer - thermal transfer - monochrome  |
| Weight                  | 1.51 kg  |
| Max Media Size          | Roll (3.6cm)   |
| Max Media Size (Custom) | 36 mm  |
| Print Speed             | Up to 80 mm/sec - draft  |
| Max Resolution (B&W)    | 360 x 720 dpi  |
| Interface               | USB 2.0, LAN, Wi-Fi(n), USB host   |
| Language Simulation     | EPSON ESC/P  |
| Barcodes                | Code 39, GS1 DataBar, QR code, MaxiCode, Aztec code, UPC-A, UPC-E, Codabar, Code 128, Postnet , PDF417, Data Matrix, ITF 2 of 5, EAN-8, EAN-13, RSS-14 |
| Media Type              | Laminated tape   |
| Compatible Tapes        | TZe tape, HGe tape, HSe tape, STe tape, FLe label  |
| Networking              | Print server   |
| Dimensions (WxDxH)      | 11.8 cm x 19.2 cm x 14.6 cm  |
| General                 |  |
| Printer Type            | Label printer - thermal transfer - monochrome  |
| Printer                 |  |
| Print Speed             | Up to 80 mm/sec - draft  |
| Built-in Devices        | Cutter   |
| Interface               | USB 2.0, LAN, Wi-Fi(n), USB host   |
| Max Resolution (B&W)    | 360 x 720 dpi  |
| Language Simulation     | EPSON ESC/P  |
| Auto Cutter             | Yes  |
| Repeating Printing      | 5000 copies  |
| Barcodes                | Code 39, GS1 DataBar, QR code, MaxiCode, Aztec code, UPC-A, UPC-E, Codabar, Code 128, Postnet , PDF417, Data Matrix, ITF 2 of 5, EAN-8, EAN-13, RSS-14 |
| Media Handling          |  |
| Media Type              | Laminated tape   |
| Compatible Tapes        | TZe tape, HGe tape, HSe tape, STe tape, FLe label  |
| Max Media Size          | Roll (3.6cm)   |
| Max Media Size (Custom) | 36 mm  |

data sheet

Product information  
 Manuf. part number PTP950NWZG1  
 Manufacturer Brother



Continued

## Brother P-Touch P950NW - Label printer

|   |   |
|---|---|
| Media Sizes                               | Roll (2.4 cm), Roll (0.6 cm), Roll (1.8 cm), Roll (1.2 cm), Roll (0.9 cm), Roll (3.6cm), Roll (0.35 cm), Roll (0.58 cm), Roll (2.36 cm), Roll (1.77 cm), Roll (1.17 cm), Roll (0.88 cm), 21 x 45 mm |
| Max Printing Width                        | 32 mm   |
| Media Feeders                             | 1 x manual - 1 roll - Roll (3.6cm)  |
| <b>Networking</b>                         |   |
| Networking                                | Print server  |
| <b>Expansion / Connectivity</b>           |   |
| Connections                               | 1 x USB 2.0<br>1 x LAN - RJ-45<br>1 x USB host  |
| <b>Miscellaneous</b>                      |   |
| Cables Included                           | 1 x USB cable   |
| Media Included                            | 1 36 mm x 8 m black on white TZe tape   |
| <b>Power</b>                              |   |
| Power Device                              | Power adapter - external  |
| <b>Environmental Standards</b>            |   |
| ENERGY STAR                               | Yes   |
| <b>Dimensions &amp; Weight</b>            |   |
| Width                                     | 11.8 cm   |
| Depth                                     | 19.2 cm   |
| Height                                    | 14.6 cm   |
| Weight                                    | 1.51 kg   |
| <b>Dimensions &amp; Weight (Shipping)</b> |   |
| Width (Shipping)                          | 16.5 cm   |
| Depth (Shipping)                          | 26.6 cm   |
| Height (Shipping)                         | 33.3 cm   |
| Weight (Shipping)                         | 2.77 kg   |

data sheet