## AC Adapter Specifications

### (For Printer, Cradle and Battery Charger)

(Specified Accessories)

Item	Specification	
Model	PW-F1215-W1-xx1 <sup>*1</sup>	
Input voltage	AC100 to 240 V, 50/60 Hz	
Rated output	DC12.0 V, 1.5 A	
Operating temperature	0°C to 40°C (32°F to 104°F)	
Dimensions (W × D × H)	32.6 mm × 69.0 mm × 75.2 mm <sup>*2</sup>	
Mass	Approx. 120 g	

\*1: The model differs by country/region. See "Sale Destinations".

\*2: Excluding the cable.

# ■ AC Adapter Specifications

(For Quad Battery Charger)

(Specified Accessories)
-------------------------

Item	Specification	
Model	PW-D0940-W2	
Specified AC cable	CB-xxxx-xxx-E <sup>*1</sup>	
Input voltage	AC100 to 240 V, 50/60 Hz	
Rated output	DC9.0 V, 4 A	
Operating temperature	0°C to 40°C (32°F to 104°F)	
Dimensions (W × D × H)	53.0 mm × 114.0 mm × 37.0 mm <sup>*2</sup>	
Mass	Approx. 318 g	
*1: The model differs by country/	region. See "Sale Destinations".	

\*1: The model differs by country/region. See "Sale Destinations".\*2: Excluding the cable.

### ■ Car Charger Specifications

#### (Specified Accessories)

Item	Specification	
Model	CC-A12-A1	
Input voltage	DC12.0 V, DC24.0 V	
Rated output	DC12.0 V, 1.5 A	
Operating temperature	0°C to 40°C (32°F to 104°F)	
Dimensions (W × D × H)	107.0 mm × 38.0 mm × 20.4 mm <sup>*</sup>	
Mass	Approx. 70 g	

\*: Excluding the cable.