

DIMMER

paladin 873 031 led



Overview

- Universal dimmer for dimmable LED-Lamps for leading edge dimming OR dimmable LED
- lamps with electronic transformer for trailing edge dimming
- Wiring without neutral wire
- Flush-mounted fitting
- Minimum dimming-value adjustable
- For pushbuttons
- Installation in standard boxes behind a pushbutton possible
- Small design (13 mm)
- Easy to connect
- Memoryfunction of the last dimming value
- Softstart function
- Protection against overload, short circuit and overheat
- Easy to connect (10 cm litz wires with ferrules)
- Compensator included in delivery

Order numbers

■ **paladin**

873 031 led without neutral wire

Technische Änderungen vorbehalten.

DIMMER

paladin 873 031 led

Technical data

Supply voltage	230 V 50 Hz
Dimensions	46 x 42 x 13 mm
Mounting	Flush-mounting
Permitted ambient temperature	0°...+40°C
Type of protection	IP 20
Type of lamps	dimnable LED lamps
Types of load	LED
Control	Pushbutton (unlighted pushbuttons only)
Dimmable 230 V~ LED lamps (leading edge dimming)	4–80 W
Dimmable 230 V~ LED lamps (trailing edge dimming)	4–200 W
Dimmable 12 V~ LED lamps (trailing edge dimming) with electronic transformer, type C	1 lamp per transformer max. 4 transformers (50 W)

Technische Änderungen vorbehalten.