

PeakTech® 3127 PROD-ID: P 3127

← BACK

Universal Power Supply 3 ... 12V DC ~ 1500mA ~ Eco-Friendly

AC/DC-Adaptor in latest eco-friendly-technology. Combined with the wide range of line voltage from 100 - 240 V AC max. output current of 1500 mA and output voltage of 3 - 12 V DC; together with the included plug set of 6 pcs the adapter can be used very universal. The powerful unit is provided with short circuit protection, automatic thermal and overload cut off.

- Safety: EN 60950
- Includes adaptor to supply USB-devices



PICTURES

 [3127 L.jpg \(273.2 kB\)](#)

 [3127 R.jpg \(274.7 kB\)](#)

Input voltage	100 ... 240 V AC; 50/60 Hz; 27,7 W
Output voltage	3,0/4,5/5,0/6,0/7,5/9,0/12,0 V DC selectable
Output current	max. 1500 mA
Dimensions (WxHxD)	52 x 95 x 73 mm
Weight	140 g
EAN-13	4250569400643

