

[Products](#) [Multimeter](#) [Analogue Multimeter / Voltmeter / Amperemeter](#) [PeakTech® 3201](#)

## PeakTech® 3201 PROD-ID: P 3201

[BACK](#)

### Analog Multimeter ~ 500 V AC/DC, 10 A DC

This new analog Multimeter has a wide range of measurement functions, including AC and DC voltages, DC-current, a resistance measurement with continuity tester or a dB measurement.

- Analog mirror scale
- DC and AC voltage measurements
- DC measurement
- Resistance measurement and continuity tester
- Decibel scale
- Safety: EN-61010-1; CAT III 600 V
- Accessories: Carrying case, Test Leads, Batteries and User Manual



#### MANUAL

[PeakTech\\_3201\\_10\\_2015.pdf \(799.2 kB\)](#)

#### PICTURE

[3201\\_Front.jpg \(217.9 kB\)](#)

[3201\\_Rear.jpg \(163.7 kB\)](#)

[3201\\_Zub.jpg \(271.3 kB\)](#)

DCV	0,1 / 2,5 / 10 / 50 / 250 / 500 V; +/- 3% FS
ACV	10 / 50 / 250 / 500 V ; +/- 4% FS
DCA	5 / 50 / 500 mA / 10 A ; +/- 3% FS
Ohm	x1; x10 ; x100; x1K; x100K ; +/- 3% arc
dB	-10 ~ +56 dB
Operating voltage	2 x 1,5 V AA Battery
Dimensions (WxHxD)	100 x 155 x 45 mm
Weight	370 g
EAN-13	4250569403590

