

[Products](#) [Decade boxes, Educational & Analog Instruments](#) [Resistance Decade Box](#) [PeakTech® 3265](#)

PeakTech® 3265 PROD-ID: P 3265

[BACK](#)

LAB Decade Box with rotary switch ~ 1 Ω ... 11,111 MΩ

For the completion of our sales program in LAB decade with shielding plastic housing for education, maintenance, trouble-shooting, working standard research, design and developing. The rotary switches enables precise, decadic adjustment of the resistance-, capacitance- or inductance values.

- High accuracy
- Plastic housing for protective shielding
- 4 mm safety jacks
- Dimensions (WxHxD): 240 x 70 x 170 mm
- Weight: 1 kg



MANUAL

[PeakTech_3265_3270_3275_09-2016F.pdf \(400.6 kB\)](#)

PICTURES

[3265_L.jpg \(310.3 kB\)](#)

[3265_R.jpg \(352.1 kB\)](#)

| | |
|--------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ranges max. current 1 Ω-steps in 7 decades | 1 ~ 10 Ω; 700 mA / 10 ~ 100 Ω; 200 mA 1 ~ 10 Ω; 700 mA / 10 ~ 100 Ω; 200 mA 100 Ω ~ 1 kΩ; 70 mA / 1 ~ 10 kΩ; 20 mA 10 ~ 100 kΩ; 7 mA / 100 kΩ ~ 1 MΩ; 1 mA 1 ~ 10 MΩ; 0,11 mA |
| Accuracy | 5 % |
| EAN-13 | 4250569400780 |

