

PeakTech® 3275 PROD-ID: P 3275

[BACK](#)

Capacitance, LAB Decade Box with rotary switch ~ 0,1nF ... 11,111 µF

For the completion of our sales program in LAB decade with shielding plastic housing for education, maintenance, trouble-shooting, working standard research, design and developing. The rotary switches enables precise, decadic adjustment of the resistance-, capacitance- or inductance values.

- High accuracy
- Plastic housing for protective shielding
- 4 mm safety jacks
- Dimensions (WxHxD): 240 x 70 x 170 mm
- Weight: 1 kg



MANUAL

[PeakTech 3265 3270 3275 09-2016F.pdf \(400.6 kB\)](#)

PICTURES

[3275_L.jpg \(385.8 kB\)](#)

[3275_R.jpg \(300.8 kB\)](#)

Ranges max. voltage 100 pF-steps in 5 decades	0,1 ~ 1 nF / 1 ~ 10 nF / 10 - 100 nF 0,1 ~ 1 nF / 1 ~ 10 nF / 10 - 100 nF 100 nF ~ 1 µF / 1 - 10 µF 300 V DC/230 V AC (50 Hz) for all ranges
Accuracy	5 %
Max. voltage limit	300 V DC / 230 V AC (50 Hz)
EAN-13	4250569400803

