

PeakTech® 3285 PROD-ID: P 3285

[BACK](#)

Capacitance Decade Box with slide switch ~ 100 pF ... 11,111 µF

This decade for capacitance is characterized by their long-term stability and is designed for the area of education, maintenance, production testing and also research and development. The housing is made of impact resistant ABS plastic and easy to use slide switches for adding and subtracting of the output values and 4 mm safety sockets for a safe connection.



MANUAL

[PeakTech_3280_3285_3290_072017F.pdf \(404.8 kB\)](#)

PICTURES

[3285_L.JPG \(276.7 kB\)](#)

[3285_R.JPG \(271.2 kB\)](#)

Ranges	100 pF ... 11,111 µF (100 pF steps) with five decades
Accuracy	5 % bei / at < 1 µF, 1 kHz / > = 1 µF, 100 Hz test frequency
Voltage limit	50 V DC non-polarized capacitors
Internal residual capacitance	50 pF max.
Accessories	operation manual
Dimensions (WxHxD)	140 x 190 x 80 mm
Weight	350 g
EAN-13	4250569402210

