

PeakTech® 5186 PROD-ID: P 5186

[BACK](#)

USB-Datalogger ~ Voltage: 0 ... 30V DC ~ 32.000 Points

The PeakTech 5186 is a data logger for DC voltages from 0 V to 30 V with terminals on the top of the device.

The included software allows to set all required parameters before recording, such as the desired sample rate, the starting function, even after a specific time and date or to set a password for securing the data access.

The measurement values recorded can be conclusively evaluated with the PC software, such as displayed as diagrams or saved as an Excel spreadsheet, text or image file.

- Data logger with internal memory up to 32,000 readings
- DC-Voltage measurement up to 30 V
- LCD for measurement values
- Sampling rate of 2 seconds up to 24 hours
- User replaceable lithium battery
- Recording time up to 2 years at 1 Sample/min
- Accessories: Software for Windows XP / Vista / 7/8/10, Required Sensor, Wall Holder, Protective Cap, Manual



MANUAL

[PeakTech 5185_86_87 Driver Installation Windows 10.pdf \(660.6 kB\)](#)

[PeakTech 5185-5186-5187_07_2019F.pdf \(4,506.8 kB\)](#)

[PeakTech 5185-5186-5187 ES.pdf \(401.0 kB\)](#)

[PeakTech 5185-5186-5187 FR_07_2019F.pdf \(685.4 kB\)](#)

PICTURES

[5186 Complete.jpg \(788.7 kB\)](#)

[5186 Front.jpg \(187.5 kB\)](#)

[5186 Rear.jpg \(203.0 kB\)](#)

SOFTWARE

[Windows Driver_P5185_5186_5187.rar \(916.5 kB\)](#)

[Windows Software_English_PeakTech 5185_5186_5187.zip \(16,352.8 kB\)](#)

Windows Software Francais PeakTech
5185_5186_5187.zip (16,314.2 kB)

DC Voltage	0.00 ... 30.00 V DC +/- 1 % + 6 dgt.
Internal Memory	32000 Values
Operating Voltage	3,6 V Lithium Battery 1200 mAh
Battery Life	Max. 2 Years @ 1 Sa/min
IP Code	IP 20
Dimensions (WxHxD)	38 x 129 x 22 mm
Weight	approx. 60 g
EAN-13	4250569403552

