

## PeakTech® 8102 PROD-ID: P 8102

[BACK](#)

### Measurement Equipment Set "Service"

For daily use in the service area designed, this case system contains everything needed for installation and maintenance of all electrical installations and other systems in the industrial and crafts area.

The PeakTech 2025 Digital Multimeter is suited for a high variety of measurements of electronics, such as AC and DC voltage, current, capacity, resistances, frequencies and temperatures. The device also has a USB port for data recording of all measured values to the PC.

The PeakTech 4945 IR-Thermometer enables rapid, simple and accurate measurement of surface temperatures, with laser pointer for noncontact, fast temperature measurement of hot or moving objects or difficult measuring points from a safe distance. In addition, this device has a temperature differential measurement function with 3-color LED.

For the inspection of inaccessible places this measurement equipment kit contains the new PeakTech 5600 video endoscope camera. This device has a flexible camera with 100cm shaft length, a removable 3.5 "color TFT display and can be used for both, photos and videos for recording to the included SD card.

These high-quality measurement devices can be safely transported to your working site with the PeakTech 7310 carrying case and protected from dust and rain, as well as from hard knocks and impact damage.



PICTURE

[8102\\_Front.jpg \(639.6 kB\)](#)

PeakTech 2025	Digital Multimeter with USB Interface ACV / DCV / ACA / DCA / Freq. / Cap. / Temp. / Contiuity / Diode / Resistance
PeakTech 4945	IR- Differential Themometer ; -50° C ... +380° C
PeakTech 5600	Video Borescope ; 8.9 mm Camera ; with SD-Card
PeakTech 7310	Carrying Case for measurement devices ; 460 x 330 x 150 mm
EAN-13	4250569403514

