

PeakTech® TK-250/100 PROD-ID: P TK-250 100

[BACK](#)

Oscilloscope Probe, 250 MHz, 100:1

A wide spectrum of professional testprobes in excellent quality and modern design. A complete set of accessories is enclosed. Suitable for any oscilloscope in the trade.



MANUAL

[PeakTech TK 60 100 250 250 100 d e f 10-2015.pdf \(414.6 kB\)](#)

PICTURE

[TK 250 100.jpg \(335.8 kB\)](#)

Bandwidth	DC 250 MHz 100:1
Input capacitance	5,5 pF
Input resistance	100 MΩ
Risetime	1,4 ns
Max. measuring voltage	2000 V DC or ACpp (1500 V rms)
Cable length	1,20 m
Reference position	Probe tip disconnected; oscilloscope input grounded
EAN-13	4250569400032

