

[Products](#) [Oscilloscopes](#) [Oscilloscopes Accessories](#) [PeakTech® TK-250](#)

## PeakTech® TK-250 PROD-ID: P TK-250

[BACK](#)

### Oscilloscope Probe, 250 MHz, 10:1/1:1

A wide spectrum of professional testprobes in excellent quality and modern design. A complete set of accessories is enclosed. Suitable for any oscilloscope in the trade. Spare part kit for oscilloscope probes, P TK-KIT contents: Channel identifier clip PA-105, sprung hook PA-106, ground lead PA-107, insulating tip PA-108, measuring tip PA-102, IC adaptor PF-902, adjusting tool PF-903, BNC-Adapter PF-901



#### MANUAL

[PeakTech TK 60 100 250 250 100 d e f 10-2015.pdf \(414.6 kB\)](#)

#### PICTURE

[TK 250.jpg \(290.4 kB\)](#)

Bandwidth	DC 250 MHz 10:1; DC 250 MHz 10:1; DC 6 MHz 1:1
Input capacitance	17 pF 10:1; 17 pF 10:1; 47 pF 1:1
Input resistance	10 MΩ 10:1; 1 MΩ 1:1
Risetime	1,4 ns 10:1 1,4 ns 10:1 58 ns 1:1
Max. measuring voltage	600 V DC or ACpp (10:1); 300 V DC or ACpp (1:1)
Cable length	1,20 m
Reference position	Probe tip disconnected; oscilloscope input grounded
EAN-13	4250569400025

