

PeakTech® 5315 PROD-ID: P 5315

[BACK](#)

PH meter 0.00 ... 14.00 with Backlight and replaceable probe

The new PeakTech 5315 PH measuring device with its long and thin test probe was specially developed for laboratory use and can also be used for smaller Erlenmeyer flasks and test tubes. The PH probe can be easily removed and replaced with a screw connection. For particularly good readability, the LCD display has a white backlight, which is activated automatically when the device is switched on. On the top side there is not only the on and off switch but also two potentiometers for calibration at pH 7 or pH 4 values, for which the corresponding calibration solutions are included.

- Clearly readable LCD display (max. 1999) with white backlight
- High measurement resolution of 0.01 pH
- Handy housing design with easily exchangeable probe
- Two-point calibration via potentiometer
- Long pH probe for use in laboratory operations
- Practical one-hand operation
- Replacement probe optionally available - model "P 5315 PR"
- Accessories: pH 4 and pH 7 calibration solution, plastic box, calibration screwdriver, batteries and manual



MANUAL

[PeakTech_5315_manual_04_2020.pdf \(883.6 kB\)](#)

PICTURES

[5315_Acc.jpg \(144.3 kB\)](#)
[5315_Front.jpg \(95.7 kB\)](#)
[5315_Pack.jpg \(186.6 kB\)](#)
[5315_Top.jpg \(113.6 kB\)](#)
[5315_Use.jpg \(257.2 kB\)](#)

| | |
|--------------------------|-----------------------------|
| PH Range | 0.00 ~ 14.00 |
| PH Resolution | 0.01 pH |
| Accuracy | +/- 0.1 pH |
| Temperature Compensation | 0 ~ 50°C |
| Operating voltage | 4 x 1.5 V (LR-44) Batteries |
| Dimensions (WxHxD) | 50 x 175 x 25 mm |
| Weight | 50 g |
| EAN-13 | 4250569405105 |

