

Model Number


BF 30-F

Plastic mounting adapter, 30 mm

Features

- For mounting cylindrical sensors with metal thread
- Secure mounting of the sensor via a snap lock
- Installation position defined by fixed stop
- Adjustable via slot mounting

Dimensions



Technical data	
General specifications	
Inside diameter	30 mm
Ambient conditions	
Ambient temperature	-25 85 °C (-13 185 °F)
Mechanical specifications	
Material	black polycarbonate (PC)
Construction type	For sensors with 45° chamfer

Note

Installation

- · Position the mounting bracket on the desired place
- Mark the position of drilling holes in the mid section of the oblong holes
- Drill the mounting holes through the surface
- Screw on the mounting bracket slightly via the lateral oblong holes by using suitable M4 screws
- Stick the sensor through the mounting bracket and fix the sensor by the lid on the upper part of the bracket
- Adjust the bracket and make the final positioning
- Fix the mounting bracket finally with the screws

www.pepperl-fuchs.com