

SMART AIR PURIFIER WITH UV-C

 velleman.eu/products/view

AIRP002



Features

- this air purifier uses UV-C light to safely eliminate viruses, bacteria, germs and mildew
- filters up to 99.5% of dust, pollen, smoke, odours, mold spores and pet dander
- with smart wifi (Tuya compatible)
- continuous air quality monitoring: 4 led colours indicate air quality, fan speed adjusts automatically according to air quality
- simple operation with touch buttons
- recommended for rooms up to 70 m²
- child lock
- filter replacement indicator
- low noise
- compatible with Alexa Home and Google Assistant

Specifications

Physical Properties

Surface Area 70 m²

Power Cord Length 1.8 m

Electrical Data

Power Rating 60 W

Technical Data

Mounting Type Free Standing

Filtration Type HEPA Class E12

Set-up Options

Number of Speed Settings 4

Environmental Data

Air Purifier Capacity 350 m³/h

Sound Level 46 dB

Operational Properties

Instruction Manual Languages Dutch, English, French, German, Polish, Portuguese, Spanish

Power Supply

Input Voltage Rating 220-240 V

Input Frequency Rating 50 Hz

Included

Removable Tank

Product Basic Info

Colour White

Height 445 mm

Depth 220 mm

Width 350 mm

Weight 5800 g

