

# TWO-IN-ONE AIR PURIFIER AND DEHUMIDIFIER

---

 [velleman.eu/products/view](https://velleman.eu/products/view)

AIRPD001



## Product description

---

No matter how often you clean and vacuum your home, the air in it will always contain dust, pet dander, pollen and sometimes allergenic or even toxic particles. Apart from these particles, a humid environment may also be harmful to your health, as dust mites, mold, mildew and other allergens thrive in areas where moisture can build up.

Our two-in-one air purifier and dehumidifier runs quietly in the background to offer you the best of both worlds: while the HEPA air purifier uses a fan to trap all those airborne particles and projects purified air into the room, the dehumidifier removes excessive humidity in your bathroom, kitchen or any other room and makes the air inside fresher and healthier.

## Features

---

- two-in-one air purifier and dehumidifier with HEPA filter
- simple operation with touch buttons and LED indicators
- the air purifier removes 99.7% of PM2.5 particles, dander, pollen, mold
- recommended for rooms up to 25 m<sup>2</sup>
- full tank LED indicator: the device stops working when water tank is full
- the removable water tank can be easily emptied and cleaned
- easy filter replacement
- low noise

## Specifications

---

## Physical Properties

Surface Area	20 m <sup>2</sup>
--------------	-------------------

---

Power Cord Length	1.5 m
-------------------	-------

---

Water Tank Capacity	1 l
---------------------	-----

## Electrical Data

Power Rating	45 W
--------------	------

## Technical Data

Mounting Type	Free Standing
---------------	---------------

---

Filtration Type	HEPA Class E11
-----------------	----------------

## Set-up Options

Number of Speed Settings	2
--------------------------	---

## Environmental Data

Air Purifier Capacity	35 m <sup>3</sup> /h
-----------------------	----------------------

---

Dehumidifying Capacity	750 ml/d
------------------------	----------

---

Sound Level	38-50 dB
-------------	----------

## Operational Properties

Instruction Manual Languages	Dutch, English, French, German, Polish, Portuguese, Spanish
------------------------------	---

## Power Supply

Input Voltage Rating	100-240 V
----------------------	-----------

---

Input Frequency Rating	50/60 Hz
------------------------	----------

## Included

Removable Tank
----------------

## Product Basic Info

Colour	White
--------	-------

---

Additional Colour	Grey
-------------------	------

### Product Basic Info

Height	31.5 cm
Depth	21.4 cm
Width	19.6 cm
Weight	2.7 kg
Material	ABS