

# FLOOR FAN - DRUM - METAL - Ø 60 cm - BLACK

---

 [velleman.eu/products/view](https://velleman.eu/products/view)

CFANo460



## Specifications

---

### Physical Properties

Coating Type Powder Coating

---

Cable Length 2 m

---

Blade Material Aluminium

### Technical Data

Cable Type H05VV-F 3G0.75

---

Mounting Type Floor stand

---

Number of Blades 3

### Set-up Options

Adjustable Height

---

Adjustable Pan

---

Adjustable Tilt

---

Oscillating Function

---

## Set-up Options

---

Number of Speed Settings 2

## Environmental Data

IP Rating IP40

---

Sound Level 87 dB

## Operational Properties

Tilt Angle 350 °

## Power Supply

Batteries

---

Rechargeable Battery

---

Input Voltage Rating VAC 220-240 V

---

Power Consumption 330 W

---

Rechargeable

## Included

Timer

---

Mist Function

## Product Basic Info

Colour Black

---

Height 75.5 cm

---

Depth 27 cm

---

Width 72.5 cm

---

Diameter 600 cm

---

Weight 22.5 kg

---

Material Metal

