

FLOOR FAN- DRUM - METAL - Ø 75 cm - BLACK

 velleman.eu/products/view

CFAN0475



Specifications

Physical Properties

Coating Type Powder Coating

Cable Length 2 m

Blade Material Aluminium

Technical Data

Cable Type H05VV-F 3G0.75

Mounting Type Floor stand

Number of Blades 3

Set-up Options

Adjustable Height

Adjustable Pan

Adjustable Tilt

Oscillating Function

Number of Speed Settings 2

Environmental Data

IP Rating IP40

Sound Level 84 dB

Operational Properties

Tilt Angle 350 °

Power Supply

Batteries

Rechargeable Battery

Input Voltage Rating VAC 220-240 V

Power Consumption 315 W

Rechargeable

Included

Timer

Mist Function

Product Basic Info

Colour Black

Height 92.5 cm

Depth 34 cm

Width 90 cm

Diameter 75 cm

Weight 35.5 kg

Material Metal