

# DIGITAL THERMOSTAT

---

 [velleman.eu/products/view](http://velleman.eu/products/view)

CTH406



## Features

---

- up to 24 time zones per day
- 3 temperature levels (comfort / energy-saving / holiday (anti-freeze))
- manual override function
- manual on/off switch

## Specifications

---

- temperature range: 5 °C - 30 °C
- rated power: 230 VAC 50 Hz 6 (2) A, max. 1380 W
- power supply: 2 x AA batteries LR6: HIGH-ENERGY ALKALINE AA / LR6 1.5V-2600mAh 4906.121.354 (4.pcs/shrink)
- size: 125 x 90 mm
- weight: 150 g