

# WIRELESS DOOR BELL

---

 [velleman.eu/products/view](https://velleman.eu/products/view)



## Features

---

- easy installation via auto-learning code button
- 36 melodies and adjustable volume (high - medium - low)
- kit includes 1 receiver + 1 transmitter, supports up to 4 transmitters (order code EDB8/TX)
- receiver: for indoor use

## Specifications

---

### Physical Properties

Number of Chimes	36
Width Doorbell Button	10.5 mm
Height Doorbell Button	10.5 mm
Depth Doorbell Button	3 cm

### Electrical Data

Quiescent Current Receiver	< 0.2 mA
Quiescent Current Transmitter	< 0.005 mA
Transmitting Current	< 15 mA
Transmitting Power	<= 10 mW

## Technical Data

Mounting Type Free Standing, Hanging

---

Auto Learning

---

Kinetic Push Button

---

Wireless

## Environmental Data

IP Rating IP20

---

Sound Level  $\geq 80$  dB

---

Operating Range 300 m

## Operational Properties

Instruction Manual Languages Dutch, English, French, German, Polish, Portuguese, Spanish

## Power Supply

Number of Batteries 3

---

Battery IEC Size AA (LR6, R6, FR6, HR6, KR6, ZR6, 15A, 15D, 15LF, 1.2H2, 1.2K2, UM3, Pencil, MN1500, MX1500, MV1500), CR2032 (5004LC)

---

Battery Composition Alkaline, Lithium

---

Battery Voltage Rating 3 V

---

Battery Type Transmitter CR2032 (5004LC)

---

Batteries Included Transmitter

---

Batteries Included Receiver

---

Number of Batteries Transmitter 1

---

Battery Type Receiver AA (LR6, R6, FR6, HR6, KR6, ZR6, 15A, 15D, 15LF, 1.2H2, 1.2K2, UM3, Pencil, MN1500, MX1500, MV1500)

---

---

**Power Supply**

---

Number of Batteries Receiver 2

---

Voltage Rating 3 V

**Included**

LED Indicator

**Product Basic Info**

Colour Black

---

Additional Colour White

---

Height 10.5 cm

---

Depth 3 cm

---

Width 10.5 cm

---

Weight 147 g