

WIRELESS BATTERY OPERATED DOOR BELL KIT WITH 2 PUSH BUTTONS

 vulleman.eu/products/view

EDMTW

This item cannot be sold in: *Switzerland*



Specifications

Physical Properties

Number of Chimes 32

Width Doorbell Button 3.3 cm

Height Doorbell Button 8.2 cm

Depth Doorbell Button 2 cm

Technical Data

Mounting Type Hanging, Table stand

Auto Learning

Kinetic Push Button

Wireless

Environmental Data

IP Rating IP44

Environmental Data

Operating Range 150 m

Operational Properties

Instruction Manual Languages Dutch, English, French, German, Polish, Portuguese, Spanish

Power Supply

Number of Batteries 4

Battery IEC Size AA (LR6, R6, FR6, HR6, KR6, ZR6 ,15A, 15D, 15LF, 1.2H2, 1.2K2, UM3, Pencil, MN1500, MX1500, MV1500), CR2032 (5004LC)

Battery Composition Alkaline, Lithium

Battery Voltage Rating 3 V

Battery Type Transmitter CR2032 (5004LC)

Batteries Included Transmitter

Batteries Included Receiver

Number of Batteries Transmitter 1

Battery Type Receiver AA (LR6, R6, FR6, HR6, KR6, ZR6 ,15A, 15D, 15LF, 1.2H2, 1.2K2, UM3, Pencil, MN1500, MX1500, MV1500)

Number of Batteries Receiver 3

Voltage Rating 1.5 V

Included

LED Indicator

Product Basic Info

Product Basic Info

Colour White

Height 11.6 cm

Depth 3.6 cm

Width 6.6 cm

Weight 160 g