

# WIRELESS PLUG-IN DOOR BELL KIT WITH 1 PUSH BUTTON

---

 [velleman.eu/products/view](https://www.velleman.eu/products/view)

This item cannot be sold in: *Switzerland*



## Specifications

---

### Physical Properties

Number of Chimes	32
------------------	----

---

Width Doorbell Button	3.3 cm
-----------------------	--------

---

Height Doorbell Button	8.2 cm
------------------------	--------

---

Depth Doorbell Button	2 cm
-----------------------	------

### Technical Data

Mounting Type	Hanging
---------------	---------

---

Auto Learning	
---------------	--

---

Kinetic Push Button	
---------------------	--

---

Wireless	
----------	--

### Environmental Data

IP Rating	IP44
-----------	------

---

Operating Range	150 m
-----------------	-------

## Operational Properties

Instruction Manual  
Languages

Dutch, English, French, German, Polish, Portuguese,  
Spanish

### Power Supply

Battery IEC Size	CR2032 (5004LC)
Battery Composition	Lithium
Battery Voltage Rating	3 V
Battery Type Transmitter	CR2032 (5004LC)
Batteries Included Transmitter	
Batteries Included Receiver	
Number of Batteries Transmitter	1
Voltage Rating	230 V

### Included

LED Indicator

### Product Basic Info

Colour	White
Height	11.6 cm
Depth	3.6 cm
Width	6.6 cm
Weight	128 g