

# PIR MOTION DETECTOR - E27 socket

---

 [velleman.eu/products/view](http://velleman.eu/products/view)

EMS107



## Features

---

- with automatic day/night detection
- adjustable: activation period, light sensitivity (TIME - LUX)

## Specifications

---

- switch type: relay
- detection angle: 360°
- detection range: 6 m (< 24 °C)
- rated load:
  - tungsten: max. 60 W (E27) - max. 0.3 A
  - fluorescent: max. 60 W (E27) - max. 0.3 A
  - led: max. 25 W - max. 4.5 A
- power supply: 110-240 V~ 50/60 Hz
- working temperature: -10 °C to +40 °C
- working humidity: < 93 % RH
- time-delay switch: 10 sec ± 3 sec to 5 min ± 2 min (adjustable)
- light sensitivity: < 10 lx - 2000 lx
- cable length: -
- dimensions: Ø 56 x 118 mm
- weight: 75.8 g

