

MINI PIR SENSOR WITH ALARM

 velleman.eu/products/view



Features

- chime / alarm function
- sensor alarm

Specifications

- operation modes: alarm / off / chime
- switch type: relay
- detection angle: 60°
- detection range: 8 m (< 24 °C)
- rated load:
 - tungsten: -
 - fluorescent: -
 - led: -
- power supply: 9 VDC 6LR61
- working temperature: -10 °C to +40 °C
- working humidity: < 93 % RH
- time-delay switch: -
- light sensitivity: -
- cable length: -
- dimensions: 109 x 73 mm
- weight: 48 g