

# DAY/NIGHT CONTROL SWITCH WITH TIMER

---

 [velleman.eu/products/view](https://velleman.eu/products/view)

EMS113



## Features

---

light control sensor with timer

## Specifications

---

- switch type: relay
- detection angle: -
- detection range: -
- rated load:
  - tungsten: max. 2000 W - max. 9 A
  - fluorescent: max. 1000 W - max. 4.5 A
  - led: max. 1000 W - max. 4.5 A
- power supply: 220-240 V~ 50/60 Hz
- working temperature: -10 °C to +40 °C
- working humidity: < 93 % RH
- time-delay switch: dusk to dawn, 1, 3, 5, 7 hours (adjustable)
- fixed light control:
  - on: < 10 lx
  - off: > 40 lx
- cable length: -
- dimensions: 26 x 100 x 70 mm
- weight: 100 g
- IP rating: IP44

