

SMART CONVECTOR HEATER - 2000 W

 velleman.eu/products/view

SMART1310



Product description

Make controlling your environment easier with the new Perel Smart range. A central app on your smartphone allows you to remotely manage an array of appliances. No more switching on or off your lighting manually, or wondering who rang at your doorbell when you were not at home. With the ever-growing Smart range you will be able to control your appliances at ease.

Tuya intelligence inside - Life has never been easier with only one app
Everyone can automate the Perel Smart range using the user-friendly and free Tuya app. Your own smartphone is the perfect gateway to live life at most ease.

This smart Perel convector is ideal as additional heating. Simply control this heater through your smartphone thanks to the integrated Tuya technology or on the device. It delivers 2.000 W of heating power and is equipped with three heat settings and a thermostat. It has a built-in 24h timer. Thanks to its overheating protection, the device switches itself off immediately when it gets too hot.

Features

- 3 heat settings: 750 W - 1250 W - 2000 W
- thermostat
- overheating protection
- turbo fan
- this product is only suitable for well insulated spaces or occasional use

- Android® and iOS® compatible
- use the Tuya® app to easily control your appliances and to create timetables
- compatible with Alexa Home and Google Assistant

Specifications

Physical Properties

Display

Power Cord Length 1.4 m

Cable Included

Number of Heat Settings 3

Shape Rectangle

Heater Type Convection, Smart

Electrical Data

Protection Overheating

Technical Data

Cable Type H05VV-F 3G0.75

Mounting Type Floor stand, Free Standing

Environmental Data

IP Rating IP20

Usage Location indoor only

Operational Properties

Instruction Manual Languages Dutch, English, French, German, Polish, Portuguese, Spanish

Switch Type Relay

Dust Filter

Heat Settings 1250 W, 2000 W, 750 W

Tip-Over Protection

Heating Area 60 m³

Heating Distance 2 m

Electrical Connections

Mains Plug Type Germany (Schuko)

IT Connections

Smart Device Compatibility Amazon Alexa, Android, Google Assistant, iOS, Tuya App

Power Supply

Input Voltage Rating VAC	220-240 V
--------------------------	-----------

Input Frequency Rating	50/60 Hz
------------------------	----------

Power Consumption	2000 W
-------------------	--------

Included

Remote Control

Timer

Thermostat

Wheels

Handle

Product Basic Info

Colour	White
--------	-------

Additional Colour	Black
-------------------	-------

Height	375 mm
--------	--------

Depth	210 mm
-------	--------

Width	605 mm
-------	--------

Weight	3.2 kg
--------	--------

Material	Metal
----------	-------

Additional Material	ABS, PP (Polypropylene)
---------------------	-------------------------