

# FAN HEATER - 2000 W - WHITE

---

 [velleman.eu/products/view](https://velleman.eu/products/view)

TC78020N



## Product description

---

This Perel fan heater is ideal as an additional heater. It delivers 2,000 W of heating power and is equipped with two heat settings, a fan function and a thermostat. Thanks to its overheating protection, the device switches itself off immediately when it gets too hot. There is a handle at the top so you can move the unit easily.

## Features

---

- 2 heat positions
- fan function
- thermostat
- handle on top
- overheating protection
- This product is only suitable for well insulated spaces or occasional use.

## Specifications

---

### Physical Properties

Display

---

Cable Included

---

Number of Heat Settings 2

---

## Physical Properties

---

Shape	Oval
-------	------

---

Heater Type	Fan
-------------	-----

## Electrical Data

Protection Overheating

## Technical Data

Mounting Type Floor stand, Free Standing, Table stand

## Environmental Data

---

IP Rating	IP20
-----------	------

---

Usage Location indoor only

## Operational Properties

---

Instruction Manual Languages	Dutch, English, French, German, Polish, Portuguese, Spanish
------------------------------	---

---

Switch Type	Rocker
-------------	--------

---

Heat Settings	1700 W, 2000 W
---------------	----------------

---

Fan Function

---

---

Heating Area	82 m <sup>3</sup>
--------------	-------------------

---

Heating Distance	1 m
------------------	-----

## Electrical Connections

Mains Plug Type Germany (Schuko)

## Power Supply

---

Input Voltage Rating VAC	220-240 V
--------------------------	-----------

---

Input Frequency Rating	50 Hz
------------------------	-------

---

Power Consumption	2000 W
-------------------	--------

## Included

---

Remote Control

---

## Included

---

Timer

---

Thermostat

---

Wheels

---

Handle

## Product Basic Info

Colour                      White

---

Height                      265 mm

---

Depth                      132 mm

---

Width                      217 mm

---

Weight                      1 kg

---

Material                      Flame Retardant PP (Polypropylene)

---

Additional Material      Copper