

Philips

Curved LCD monitor with Ultra Wide-Color

E Line

32 (31.5"/80 cm diag.) 3840 x 2160 (4K UHD)

328E1CA

Simply immersive

The 32" curved E line display offers a truly immersive experience in a stylish design. Ultraclear 4K UHD with Ultra Wide-Color and Adaptive-Sync brings your images alive!

Curved design inspired by the world around us

• Curved display design for a more immersive experience

Superb Picture Quality

- Ultra Wide-Color wider range of colours for a vivid picture
- VA display delivers awesome images with wide viewing angles
- UltraClear 4K UHD (3840 x 2160) resolution for precision
- Effortlessly smooth action with Adaptive-Sync technology
- SmartContrast for rich black details

Features designed for you

- Cable management reduces cable clutter for a neat workspace
- · Less eye fatigue with Flicker-Free technology
- · LowBlue Mode for easy-on-the-eyes productivity
- · HDMI ensures universal digital connectivity
- Built-in stereo speakers for multimedia
- DisplayPort connection for maximum visuals



Highlights

Curved display design



Desktop monitors offer a personal user experience, which suits a curved design very well. The curved screen provides a pleasant yet subtle immersion effect, which focuses on you at the centre of your desk.

Ultra Wide-Color Technology





Ultra Wide-Color Technology delivers a wider spectrum of colours for a more brilliant picture. The Ultra Wide-Color wider "colour gamut" produces more natural-looking greens, vivid reds and deeper blues. Bring media entertainment, images and even productivity more alive with vivid colours from Ultra Wide-Color Technology.


VA display



The Philips VA LED display uses an advanced multi-domain vertical alignment technology that gives you super-high static contrast ratios for extra-vivid and bright images. While standard office applications are handled with ease, it is especially suitable for photos, web browsing, films, gaming and demanding

graphical applications. Its optimised pixel management technology gives you a 178/178 degree extra-wide viewing angle, resulting in crisp images.

UltraClear 4K UHD Resolution



These Philips displays utilise high-performance panels to deliver UltraClear, 4K UHD (3840 x 2160) resolution images. Whether you are a demanding professional requiring extremely detailed images for CAD solutions, a user of 3D graphics applications or a financial wizard working on huge spreadsheets, Philips displays will make your images and graphics come alive.

Adaptive-Sync technology



Gaming shouldn't be a choice between choppy gameplay or broken frames. Get fluid, artefactfree performance at virtually any frame rate with Adaptive-Sync technology, smooth quick refresh and ultra-fast response time.

SmartContrast



SmartContrast is a Philips technology that analyses the contents you are displaying,

automatically adjusting colours and controlling backlight intensity to dynamically enhance contrast for the best digital images and videos or when playing games where dark hues are displayed. When Economy mode is selected, contrast is adjusted and backlighting fine-tuned for just-right display of everyday office applications and lower power consumption.

Concealed cables



For a cleaner workspace, this monitor features an elegant solution for cable management. No need to bundle cables with extra ties. An elongated slot provides hidden storage for cables. It conceals cables and looks great in most environments, especially for a small space or a desk facing a wall or a window. This design cleans up messy cables for a more organised desk.

Flicker-Free technology



Due to the way brightness is controlled on LED-backlit screens, some users experience flicker on their screen which causes eye fatigue. Philips Flicker-Free technology applies a new solution to regulate brightness and reduce flicker for more comfortable viewing.



















Specifications

Picture/Display

- LCD panel type: VA LCD
- · Backlight type: W-LED system
- Panel Size: 31.5 inch/80 cm
- Display Screen Coating: Anti-Glare, 3H, Haze 25% • Effective viewing area: 697.3 (H) \times 392.2 (V) mm at a 1500R curvature*
- Aspect ratio: 16:9
- Optimum resolution: 3840 x 2160 @ 60 Hz
- Pixel Density: 140 PPI
- Response time (typical): 4 ms (Grey to Grey)*
- Brightness: 250 cd/m²
- · Contrast ratio (typical): 2500:1
- SmartContrast: Mega Infinity DCR
- Pixel pitch: 0.182 x 0.182 mm
- Viewing angle: 178° (H)/178° (V), @ C/R > 10
- Flicker-free
- Picture enhancement: SmartImage game
- Colour gamut (typical): NTSC 99%*, sRGB 122%*
- Display colours: Colour support 1.07 billion colours
- Scanning Frequency: 53–84 kHz (H)/48–75 Hz (V)
- SmartUniformity: 97 ~ 102%
- Delta E: < 2
- LowBlue Mode
- sRGB
- · Adaptive sync

Connectivity

- Signal Input: DisplayPort 1.2, HDMI 2.0 x 2
- Sync Input: Separate Sync, Separate Sync (VGA only), Sync on Green
- · Audio (In/Out): PC audio-in, Audio out

Convenience

- Built-in Speakers: 3 W x 2
- · User convenience: Power On/Off, Menu, Volume, Input, SmartImage Game
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
- Other convenience: Kensington lock, VESA mount $(100 \times 100 \text{ mm})$
- Plug and Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 10 / 8.1 / 8 / 7

Stand

• Tilt: -5/20 degree

Power

- On mode: 61.1 W (typ.)
- Standby mode: < 0.5 W (typ.)
- Off mode: < 0.3 W (typ.)
- · Energy Label Class: G
- Power LED indicator: Operation White, Standby mode - White (flashing)
- Power supply: Internal, 100-240 VAC, 50-60 Hz

Dimensions

- Product without stand (mm): 709 x 425 x 88 mm
- Packaging in mm (W x H x D): 800 x 625 x 236 mm
- Product with stand (max height): $709 \times 523 \times$

Weight

- Product with stand (kg): 7.71 kg
- Product without stand (kg): 6.89 kg
- Product with packaging (kg): 10.51 kg

Operating conditions

- Temperature range (operation): 0 to 40 °C
- Temperature range (storage): -20 to 60 °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000 ft (3658 m), Nonoperation: +40,000 ft (12,192 m)
- MTBF: 50,000 hrs (excluding backlight) hour(s)

Sustainability

- Environmental and energy: RoHS, Mercury Free
- Recyclable packaging material: 100 %

Compliance and standards

• Regulatory Approvals: CCC, CECP, CEL, CE Mark, SEMKO, TUV Ergo, TUV/GS, cETLus, CU-EAC

Cabinet

- · Colour: Black
- · Finish: Textured

What's in the box?

- · Monitor with stand
- · Cables: DP cable, HDMI cable, Audio cable, Power
- User Documentation



Issue date 2022-05-16

12 NC: 8670 001 59227

EAN: 87 12581 75851 6

Version: 12.0.1

© 2022 Koninklijke Philips N.V. All Rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com

Radius of the arc of the display curvature in mm

* Response time value equal to SmartResponse * NTSC Area based on CIE 1976

* sRGB Area based on CIE1931

* The monitor may look different from feature images.