

Philips Signage Solutions Multi-Touch Display

32" Powered by Android Multi-touch

SignageSolutions

32BDL3651T

Engage them

10-point Multi-Touch display.

Inspire collaboration. Deliver information. This responsive Philips Multi-Touch Professional Full HD Display is ideal for multi-finger, multi-user applications-from wayfinding to presentations. Up to 10 touch points can be active at once.

Superb picture. Responsive touchscreen.

- Full HD. Clear images. Crisp contrast
- Plug-and-play 10-point Multi-Touch display
- Android SoC processor. Native and web apps

Effortless setup. Total control.

- CMND & Deploy. Install and launch apps remotely
- Operate, monitor and maintain with CMND & Control
- CMND & Create. Develop and launch your own content

Versatile system solution

- Energy-saving automatic backlight control
- FailOver ensures content is always playing
- Internal memory. Upload content for instant play
- · Simplified user interaction with kiosk mode



Highlights

CMND & Deploy

Quickly install and launch any app-even when you're off-site and working remotely. CMND & Deploy lets you add and update your own apps, as well as apps from the Philips Professional Display App Store. Simply scan the QR code, log in to the store, and click on the app you want to install. The app is automatically downloaded and launched.

CMND & Control



Run your display network over a local (LAN) connection. CMND & Control allows you to perform vital functions like controlling inputs and monitoring display status. Whether you're in charge of one screen or 100.

CMND & Create



Take control of your content with CMND & Create. A drag-and-drop interface makes it simple to publish your own content-whether it's a daily specials board or branded corporate information. Preloaded templates and integrated widgets ensure your stills, text, and video will be up and running in no time.

FailOver



From waiting room to meeting room, never show a blank screen. FailOver lets your Philips Professional Display switch automatically between primary and secondary inputs ensuring content keeps playing even if the primary source goes down. Simply set a list of alternate inputs to be sure your business is always on.

Internal memory

Save and play content without the need for a permanent external player. Your Philips professional display has an internal memory, which allows you to upload media into the display for instant playback. The internal memory also functions as a cache for online streaming.

Powered by Android 8

Control your display via an Internet connection. Android-powered Philips Professional Displays are optimized for native Android apps, and you can install web apps directly to the display too. A new Android 8 ensures the software is kept secure and remain to the latest specification for longer.

💦 LED



Multi-**Touch**

Specifications

Picture/Display

- Diagonal screen size: 32 inch / 80 cm
- Panel resolution: 1920x1080p
- Optimum resolution: 1920 x 1080 @ 60 Hz
- Brightness: 350 cd/m²
- Contrast ratio (typical): 4000:1
- · Surface treatment: Anti-Glare coating
- Aspect ratio: 16:9
- Response time (typical): 6.5 ms
- Pixel pitch: 0.36375(H)X0.36375(V) mm
- Display colors: 16.7 M
- Viewing angle (H / V): 178 / 178 degree
- · Panel technology: VA
- Operating system: Android 8.0
- Picture enhancement: 3/2 2/2 motion pull down, 3D Combfilter, 3D MA deinterlacing, Dynamic contrast enhancement, Motion compens. deinterlacing, Progressive scan

Interactivity

- · Multi-touch technology: Projected capacitive
- Touch points: 10 simultaneous touch points
- Plug and play: HID compliant
- · Protection glass: 2 mm tempered safety glass

Connectivity

- Video input: DVI-I (x 1), HDMI 2.0 (x2), USB 2.0 Type A (x2), USB 2.0 Type B (x1), VGA (via DVI-I) x1
- Audio input: 3.5 mm jackAudio output: 3.5mm jack
- External control: RJ45, IR (in/out) 3.5 mm jack, RS232C (in/out) 2.5 mm jack
- Other connections: micro SD

Supported Display Resolution Computer formats Resolution Refresh rate 640 x 480 60, 67, 72, 75Hz 56, 60, 72, 75Hz 800×600 1024 x 768 60H7 1280 x 768 60Hz 1280 × 800 60Hz 1280 x 1024 60Hz 1360 x 768 60H7 1366 x 768 60Hz 1440 × 900 60Hz 1600 x 1200 60Hz 1920 x 1080 60Hz 1920 x 1200 60Hz 720 x 400 70Hz 800 x 600 60, 72, 75Hz 60 Hz, 50 Hz 3840 x 2160 Video formats Resolution Refresh rate 480i 60Hz 480p 60Hz 576p 50Hz 576i 50Hz 50. 60Hz 720p 1080i 50, 60Hz 1080p 50, 60Hz 1080i 25, 30Hz

30. 60Hz

480i

576i	25, 50Hz
3840 x 2160	24, 25Hz
3840 x 2160	30Hz

Convenience

- Placement: Landscape (18/7), Portrait (18/7)
- Signal loop through: IR Loopthrough, RS232
- Network controllable: RS232, RJ45
- Screen saving functions: Pixel Shift, Low Brightness
- Keyboard control: Hidden, Lockable
- Remote control signal: Lockable
- · Energy saving functions: Smart Power

Dimensions

- Set dimensions (W x H x D): 749.1 x 443.6 x 70.4(D@Wall mount)/ 74.4(D@AC) mm Set dimensions in inch (W x H x D):
- 29.49 x 17.46 x 2.77D@Wall mount)/ 2.93(D@AC) inch • Product weight: 8.0 kg
- Product weight (lb): 17.64 lb
- Wall Mount: 100mm x 100mm, 200mm x 200mm , M4
- Bezel width: 2.0 mm (T/R/L/B)

Sound

• Built-in speakers: 2 x 10W

Operating conditions

- Temperature range (operation): 0 ~ 40 °C
- MTBF: 50,000 hour(s)
- Altitude: 0 ~ 3000 m
- Temperature range (storage): -20~60 °C
- Humidity range (operation)[RH]: 20 ~ 80%
- (without condensation) Humidity range (storage) [RH]: 5 ~ 95% (without
- condensation)

Power

- Mains power: 100 ~ 240 VAC, 50/60Hz
- Standby power consumption: <0.5W
- Consumption (Typical): 50 W
- Power Saving Features: Smart Power
- Consumption (Max): 80 W
- · Energy Label Class: G

Accessories

- Stand: BM05922 (Optional)
- Included Accessories: Cleaning cloth (x1), IR sensor cable (1.8 m) (x1), Philips logo (x1), Power supply cable (3 m), Quick start guide (x1), Remote control & AAA batteries, RS232 cable (3 m) (x1), RS232 daisy chain cable (x1), USB Cover and screw x1

Miscellaneous

- On-Screen Display Languages: Arabic, English, French, German, Italian, Japanese, Polish, Spanish, Turkish, Russian, Simplified Chinese, Traditional Chinese, Danish, Dutch, Finnish, Norwegian, Portuguese, Swedish
- Regulatory approvals: CB, CE, FCC, Class A,

PHILIPS	Issue date 2022-07-14	© 2022 Koninklijke Philips N.V. All Rights reserved.
	Version: 1.0.1	Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.
Ŧ	12 NC: 8670 001 72681 EAN: 87 12581 77394 6	www.philips.com

RoHS, BSMI, CU, ETL, IMDA, PSB • Warranty: 3 year warranty

Multimedia Applications

- USB Playback Picture: BMP, GIF, JPEG, JPG, PDF USB Playback Audio: AAC, AIF, AIFF, ASF, LPCM,
- M3U, M4A, MP3, MP4, WAV, WMA • USB Playback Video: M2TS, M4V, MK3D, MKV,
- MP4, MPEG, MPG, MTS, TS, TTS, VOB, WMV

Internal Player

- CPU: 2 x A53 + 2 x A73
- Memory: 2GB DDR3, 8GB
- GPU: ARM Mali G51
- Wifi: 2.4 G, 5 G