



Philips  
Client mounting bracket

for Philips SmartErgoBase

BS8B2325B



## Maximise desk space

Maximise desk space and secure PC clients to your Philips monitor SmartErgoBase with the client mounting stand. This simple versatile solution allows you to create an All-in-One-like setup for max productivity

### Maximise desk space

- Simple All-in-One solution
- Easy to set up and use
- Universal 100 mm VESA mounting pattern
- Full ergonomic adjustability

# PHILIPS

# Specifications

## Convenience

- VESA Mount: 100 x 100 mm

## Dimensions

- Product (W x H x D): 120 x 120 x 21 mm
- Single product with package: 156 x 60 x 131 mm

## Weight

- Product: 0.193 kg
- Single product with package: 0.25 kg
- Maximum loading (kg): 5 kg

## Operating conditions

- Temperature range (operation): 0°C to 40°C °C
- Temperature range (storage): -20°C to 60°C °C
- Relative humidity: 20%-80 %

- Altitude: Operation: +12,000 ft (3658 m), Non-operation: +40,000 ft (12,192 m)
- Lifetime: 3 years

## Sustainability

- Environmental and energy: RoHS
- Recyclable packaging material: 100 %

## Cabinet

- Colour: Black
- Finish: Texture

## Product Compatibility

- Compatible with: Philips Height Adjustment Base of 230B8\*\*\*, 240B9\*\*, 241B8\*\*\*\*, 243B9\*\*\*\*, 252B9\*\*\*\*, 245B9\*\*\*

# Highlights

## Simple All-in-One solution

This simple client mounting bracket allows for a simple low-cost solution to create a clutter-free all-in-one desktop computing form factor that makes efficient use of space-constrained environments.

## Easy to set up and use

The client mounting bracket fits right on to Philips's award-winning commercial monitor SmartErgoBase for easy PC and Thin Client mounting.

## VESA mounting pattern

Industry-standard VESA mounting holes guarantee mounting compatibility with most small form factor PCs and Thin Clients.

## Ergonomic adjustability

The client mounting bracket's clever design allows for full ergonomic adjustments (height, swivel, tilt) on the Philips SmartErgoBase



Issue date 2021-07-14

Version: 4.0.1

12 NC: 8670 001 60797  
EAN: 87 12581 76041 0

© 2021 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)