

PIN CONNECTORS



BU-192120001

BU-192120003

BU-192120005

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

- Mueller offers three different pin connectors
- Vinyl insulated
- 3 AWG sizes
 - o 12-10AWG (BU-192120001)
 - o 16-14AWG (BU-192120005)
 - o 22-18AWG (BU-192120003)
- Pin diameters
 - o BU-192120001: .110in
 - o BU-192120005: .074in
 - o BU-192120003: .074in
- Quick connect style
- Max temperature rating of 75°C
- Voltage Rating: 600V
- All terminals are made of copper with tin plating
- Solid or stranded wire accepted
- Recommended strip length: ¼"
- All are UL listed