

FW95 - Total Safety Wellington S5

Collection: Portwest™ Work

Range: Footwear

Material Upper: PVC/Nitrile

Material Outsole: PVC/Nitrile

Product information

The Total Safety Wellington offers ultimate S5 protection to the wearer. Steel toecap and midsole. PVC/Nitrile construction that is waterproof and resistant to oil, fuels and acids. Suitable for a variety of environments.

Standards

EN ISO 20345: 2011 S5

EN 13832-3: 2018

AS 2210.3

ASTM F2413-18

Portwest™ Work

Complete range of styles made of polymeric materials. Durable and waterproof construction that is highly resistant to fuels, oils, grease and fats.

Footwear

Innovation, design, styling and quality components define the Portwest foot protection collection.

Features

- Kick spur
- Reinforced ankle protection
- Fully waterproof
- Dual density PVC/Nitrile construction
- Chemical resistant
- Protective steel toecap
- Pierce resistant steel midsole
- Anti-static footwear
- Energy Absorbing Seat Region
- 100% Waterproof to keep feet dry
- SRC - Slip resistant outsole to prevent slips and trips on ceramic and steel surfaces



FW95 - Total Safety Wellington S5
Commodity Code: 6401100000

Test House

Intertek Italia S.p.A. (Notified Body No.: NB: 2575)

Via Guido Miglioli 2/A,

-, Italy

Cert No: LECFI00372281

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
FW95BKR36	Black	44.0	44.0	44.0	2.0000	0.0852	5036108212217	15036108697899
FW95BKR37	Black	44.0	44.0	44.0	1.9500	0.0852	5036108159741	15036108632500
FW95BKR38	Black	44.0	44.0	44.0	2.0600	0.0852	5036108159758	15036108632517
FW95BKR39	Black	44.0	44.0	44.0	2.0300	0.0852	5036108159765	15036108632524
FW95BKR40	Black	44.0	44.0	44.0	2.0000	0.0852	5036108159772	15036108632531
FW95BKR41	Black	44.0	44.0	44.0	2.3200	0.0852	5036108159789	15036108632548
FW95BKR42	Black	44.0	44.0	44.0	2.2800	0.0852	5036108159796	15036108632555
FW95BKR43	Black	44.0	44.0	44.0	2.3900	0.0852	5036108159802	15036108632562
FW95BKR44	Black	44.0	44.0	44.0	2.5200	0.0852	5036108159819	15036108632579
FW95BKR45	Black	44.0	44.0	44.0	2.5900	0.0852	5036108159826	15036108632586
FW95BKR46	Black	44.0	44.0	44.0	2.0000	0.0852	5036108159833	15036108632593
FW95BKR47	Black	44.0	44.0	44.0	2.7000	0.0852	5036108159840	15036108632609
FW95BKR48	Black	44.0	44.0	44.0	2.9000	0.0852	5036108203031	15036108690371
FW95BKR49	Black	44.0	44.0	44.0	2.9600	0.0852	5036108252039	15036108740762