

A140 - Thermal Grip Glove - Latex

Collection: Thermal Protection Gloves

Range: Hand Protection

Materials: Acrylic, Elastic, Polyester

Dipping:

Inner Pack: 12

Outer Carton: 144

Product information

The Thermal Grip Glove is perfect for construction, transportation, refuse collection, maintenance and local authority work. This glove has a warm acrylic 10 gauge liner and is ideal for more heavy duty, outdoor tasks or those people working in cold conditions.



Thermal Protection Gloves

When cold thermal hazards are present, the hands' motor skills can be greatly reduced, this leads to increased risk of accidents and injury. Specially designed thermal protective gloves are available to combat these dangers in hazardous environments.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 4
 EN 388: 2016 + A1: 2018 (1141X)
 EN 511: 2006 (X1X)
 ANSI/ISEA 105: 2016 CUT Level (A1)



Features

- Specially designed for use in cold conditions
- Palm dipped to increase dexterity and ventilation
- Crinkle latex grip offers excellent grip
- Warm 10 gauge acrylic liner for cold protection
- Breathable seamless liner
- Ergonomically designed for comfort and ease of use
- Retail tag which aids presentation for retail sales
- CE certified
- UKCA marked
- ANSI cut level A1

A140 - Thermal Grip Glove - Latex
Commodity Code: 6116102091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/20610-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
 SATRA Technology Park
 NN16 8SD, United Kingdom
 Cert No: AB0321/18539-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
A140BKRXS	Black	45.0	30.0	52.0	0.0780	0.0702	5036108210671	15036108696106
A140BKRS	Black	45.0	30.0	52.0	0.0960	0.0702	5036108174607	15036108603555
A140BKRM	Black	45.0	30.0	52.0	0.0980	0.0702	5036108155446	15036108603548
A140BKRL	Black	45.0	30.0	52.0	0.1000	0.0702	5036108155453	15036108603531
A140BKRXL	Black	45.0	30.0	52.0	0.1160	0.0702	5036108155460	15036108603562
A140BKRXL	Black	45.0	30.0	52.0	0.1280	0.0702	5036108166169	15036108603579

