

FW74 - Safety Chest Wader S5

Collection: Portwest™ Work

Range: Footwear

Material Upper: PVC/Nitrile

Material Outsole: PVC/Nitrile

Product information

Heavy duty pvc/nitrile safety wader with steel toecap and steel midsole. Colour coded red outsole for easy identification of safety features.

Standards

EN ISO 20345: 2011 S5



Portwest™ Work

Complete range of styles made of polymeric materials. Durable and waterproof construction that is highly resistant to fuels, oils, grease and fats.

Footwear

Innovation, design, styling and quality components define the Portwest foot protection collection.

Features

- Adjustable waist and straps
- Stainless steel eyelets
- Kick spur
- Colour coded red outsole for easy identifications of safety features
- 100% Waterproof to keep feet dry
- Pierce resistant steel midsole
- CE certified
- UKCA marked
- Protective steel toecap
- Anti-static footwear
- Energy Absorbing Seat Region



FW74 - Safety Chest Wader S5
Commodity Code: 6401990010

Test House

Intertek Italia S.p.A. (Notified Body No.: NB: 2575)

Via Guido Miglioli 2/A,

-, Italy

Cert No: LECFI00372281

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
FW74BKR37	Black	44.0	44.0	32.0	2.6400	0.0620	5036108199228	15036108684998
FW74BKR38	Black	44.0	44.0	32.0	2.8200	0.0620	5036108199235	15036108685001
FW74BKR39	Black	44.0	44.0	32.0	2.7500	0.0620	5036108199242	15036108685018
FW74BKR40	Black	44.0	44.0	32.0	2.9100	0.0620	5036108199259	15036108685025
FW74BKR41	Black	44.0	44.0	32.0	3.0600	0.0620	5036108199266	15036108685032
FW74BKR42	Black	44.0	44.0	32.0	3.1200	0.0620	5036108199273	15036108685049
FW74BKR43	Black	44.0	44.0	35.0	3.3700	0.0678	5036108199280	15036108685056
FW74BKR44	Black	44.0	44.0	35.0	3.3400	0.0678	5036108199297	15036108685063
FW74BKR45	Black	44.0	44.0	35.0	3.5200	0.0678	5036108199303	15036108685070
FW74BKR46	Black	44.0	44.0	35.0	3.5100	0.0678	5036108199310	15036108685087
FW74BKR47	Black	44.0	44.0	35.0	3.5700	0.0678	5036108199327	15036108685094
FW74BKR48	Black	44.0	44.0	35.0	3.6000	0.0678	5036108310128	15036108798732

