

C496 - Madrid Hi-Vis Half Mesh Executive Vest

Collection: Vest-Port

Range: High Visibility

Shell Fabric: 100% Polyester, Warp Knit

Inner Pack: 10

Outer Carton: 60

Product information

When temperatures are soaring stay visible and cool in this revolutionary garment. The mesh top allows for maximum breathability and airflow, ensuring a cool and comfortable wear.

Vest-Port

The Vest-Port™ extensive range of vests covers the varied demands of the work environment from core styles to the revolutionary "Executive" design, which is now available in both summer and winter weights.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Standards

EN ISO 20471 Class 1

ANSI/ISEA 107 TYPE R CLASS 2



Features

- Cooling mesh upper torso for increased breathability
- Front zip opening for easy access
- 7 pockets for ample storage
- Two lower patch pockets
- Reflective tape for increased visibility
- Phone and pen holder pocket
- D-ring for keys or ID cards
- Dual ID holder allows use of both portrait and landscape ID card display
- Radio loop for easy clipping of a radio
- Available in sizes from XS to 4XL
- Retail bag which aids presentation for retail sales

C496 - Madrid Hi-Vis Half Mesh Executive Vest
Commodity Code: 6110309100

Test House

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: VN605 151382

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: VN605 151382

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
C496ORRS	Orange	43.0	28.0	48.0	0.2460	0.0578	5036108285754	15036108775900
C496ORRM	Orange	43.0	28.0	48.0	0.2500	0.0578	5036108285747	15036108775894
C496ORRL	Orange	43.0	28.0	48.0	0.2380	0.0578	5036108285730	15036108775887
C496ORRXL	Orange	43.0	28.0	48.0	0.2690	0.0578	5036108285761	15036108775917
C496ORRXXL	Orange	43.0	28.0	48.0	0.2730	0.0578	5036108285778	15036108775924
C496ORRXXXL	Orange	43.0	28.0	48.0	0.2790	0.0578	5036108285785	15036108775931