

### S773 - Bizflame Rain Hi-Vis Antistatic FR Bomber Jacket

**Collection:** Bizflame™ Rain

**Range:** Flame Resistant

**Shell Fabric:** Bizflame Rain HV: 98% Polyester, 2% Carbon Fibre, Breathable PU Coated

**Outer Carton:** 12

#### Product information

This fully waterproof bomber jacket offers multi-norm protection in hazardous conditions. Features include chemical resistance and a detachable hood.

#### Bizflame™ Rain

The Multi-Protection Range is a collection of high-quality, fully certified garments that offer maximum protection to the following standards: EN ISO 20471 High Visibility, EN343 Waterproof and Breathable, EN ISO 14116 Flame Resistant, EN1149 Anti-Static.

#### Flame Resistant

This industry leading flame resistant range provides multi standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

#### Standards

EN ISO 14116 Index 3

EN 1149 -5

EN 13034 Type PB [6]

EN ISO 20471 Class 3

RIS 3279 TOM Issue 2 (Orange Only)

EN 343 Class 3:1 X



#### Features

- Flame resistant treated waterproof fabric prevents water penetration
- Anti-static
- Internal chest pocket
- Ribbed cuffs for added comfort
- Fully lined and padded to trap the heat and increase warmth
- Premium sew on flame resistant reflective tape
- Breathable fabric to draw moisture away from the body keeping the wearer cool, dry and comfortable
- Taped seams to provide additional protection
- 4 pockets for ample storage
- Phone pocket
- Two-way zip for quick and easy access

**S773 - Bizflame Rain Hi-Vis Antistatic FR Bomber Jacket**  
**Commodity Code: 6210200010**

**Test House**

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
 Bracetown Business Park  
 D15 YN2P, Ireland  
 Cert No: 2777\_14300\_01\_E00\_00

SGS FIMKO Ltd (Notified Body No.: NB: 0598)  
 Takomotie 8  
 , Finland  
 Contact: sgs.fimko@sgs.com  
 Cert No: 0598

**Wash Care**



**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	DUN14
S773YERXS	Yellow	65.0	40.0	43.0	1.5800	0.1118	5036108309603	15036108798183
S773YERS	Yellow	65.0	40.0	43.0	1.6500	0.1118	5036108207091	15036108694089
S773YERM	Yellow	65.0	40.0	43.0	1.7600	0.1118	5036108207084	15036108694072
S773YERL	Yellow	65.0	40.0	43.0	1.7700	0.1118	5036108207077	15036108694065
S773YERXL	Yellow	65.0	40.0	43.0	1.8700	0.1118	5036108207107	15036108694096
S773YERXXL	Yellow	65.0	40.0	43.0	1.8100	0.1118	5036108207114	15036108694102
S773YERXXXL	Yellow	65.0	40.0	43.0	1.9000	0.1118	5036108207121	15036108694119
S773YER4XL	Yellow	65.0	40.0	43.0	2.0100	0.1118	5036108212187	15036108697851
S773YER5XL	Yellow	65.0	40.0	43.0	2.0500	0.1118	5036108212194	15036108697868