

C030 - CE Safe-Welder Coverall

Collection: Safewelder Woven

Range: Flame Resistant

Shell Fabric: Bizweld Work: 100% Cotton

Outer Carton: 18

Product information

Offering complete protection all day long and fantastic value for money, the Safe-Welder™ Coverall is a great choice for welders and industrial workers who are exposed to heat. The side elastic gives the wearer a more comfortable fit and multiple pockets keep tools and personal belongings safe.

Safewelder Woven

This fabric is 100% preshrunk cotton drill with a unique flame resistant finish.

Flame Resistant

This industry leading flame resistant range provides multi standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Rule pocket
- Quick and easy side access
- Concealed stud front for easy access
- Stud adjustable cuffs for a secure fit
- Available in sizes from XS to 5XL
- Available in an excellent choice of corporate colours
- 40+ UPF rated fabric to block 98% of UV rays
- CE-CAT III
- CE certified

C030 - CE Safe-Welder Coverall
Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777_12872_03_E00_00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
C030RERXS	Red	0.0	0.0	0.0	0.0000	0.0000	5036108120215	
C030RERS	Red	43.0	28.0	60.0	1.1200	0.0722	5036108120222	15036108611819
C030RERM	Red	43.0	28.0	60.0	1.1600	0.0722	5036108120239	15036108611802
C030RERL	Red	43.0	28.0	60.0	1.2200	0.0722	5036108120246	15036108611772
C030RERXL	Red	43.0	28.0	60.0	1.3500	0.0722	5036108120253	15036108611833
C030RERXXL	Red	43.0	28.0	60.0	1.3400	0.0722	5036108120260	15036108611864
C030RERXXXL	Red	43.0	28.0	60.0	1.4300	0.0722	5036108120277	15036108611888
C030RER4XL	Red	0.0	0.0	0.0	0.0000	0.0000	5036108120284	