


Plugs for the world

Connector ProTOP - Part no. 125



- screw terminals
- cable gland and sealing
- strain relief and protection against kinking enclosure with thread lock and safety slide

Technical information	
Ampere	32 A
Poles	4 p
Voltage	230V
Earth position	9 h
Hertz	50-60 Hz
Connection technology	Screw terminals
Contact	standard
Protection type	IP 44



Drawing	Amp.		16			32	
3 MB 60	Poles	3	4	5	3	4	5
Dim. in mm	а	160	174	172	214	214	210
	b	57	61	69	75	75	80
	h	83	92	98	100	100	108
	y	16	16	16	22	22	22
Terminal for cond. cross		1	1	1	2,5	2,5	2,5
section (mm²) minmax.		— 2,5	— 2,5	—2,5	-6	— 6	6