AOC

AOC V4 Q32V4 computer monitor 80 cm (31.5") 2560 x 1440 pixels 2K Ultra HD LED Black

Brand : AOC   **Product family:** V4   **Product code:** Q32V4

Product name : Q32V4

Q32V4 - 31.5" IPS monitor ensuring a great picture quality with QHD resolution

AOC V4 Q32V4 computer monitor 80 cm (31.5") 2560 x 1440 pixels 2K Ultra HD LED Black:

31.5" IPS monitor ensuring a great picture quality with QHD resolution
In an extremely clean design, the Q32V4 boasts a flat 31.5" IPS display with QHD resolution. This model offers the full package with Adaptive Synch, 75Hz refresh rate, Low Blue Light and Flicker-Free.
AOC V4 Q32V4. Display diagonal: 80 cm (31.5"), Display resolution: 2560 x 1440 pixels, HD type: 2K Ultra HD, Display technology: LED, Display surface: Matt, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). VESA mounting. Product colour: Black

Display

Display diagonal *	80 cm (31.5")
Display brightness (typical)	250 cd/m²
Display resolution *	2560 x 1440 pixels
Native aspect ratio *	16:9
Response time	4 ms
HD type *	2K Ultra HD
Display technology *	LED
Backlight type	W-LED
Display surface	Matt
Screen shape *	Flat
Supported graphics resolutions	1920 x 1080 (HD 1080),2560 x 1440
Supported video modes	1080p,1440p
Aspect ratio	4:3,16:9
Contrast ratio (typical) *	1200:1
Contrast ratio (dynamic)	20000000:1
Maximum refresh rate *	75 Hz
Viewing angle, horizontal	178°
Viewing angle, vertical	178°
Display number of colours *	16.78 million colours
Panel type *	IPS
Pixel density	93 ppi
Surface hardness	3H
Colour depth	8 bit
sRGB coverage (typical)	102%
Adobe RGB coverage	75%

Performance

NVIDIA G-SYNC *	✗
AMD FreeSync *	✗
VESA Adaptive Sync support	✓
Flicker-free technology	✓

Ports & interfaces

Built-in USB hub *	✗
DVI port	✗
HDMI *	✓
HDMI ports quantity	1
HDMI version	1.4
DisplayPorts quantity	1
DisplayPort version	1.2
Audio input	✓
Headphone out *	✓
Headphone outputs	1
Headphone connectivity	3.5 mm
DC-in jack	✓

Ergonomics

Panel mounting interface	100 x 100 mm
Cable lock slot *	✓
Cable lock slot type	Kensington
VESA mounting *	✓
Height adjustment *	✗
Tilt angle range	-3.5 - 21.5°
On Screen Display (OSD)	✓
On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Italian, Japanese, Korean, Polish, Portuguese, Russian, SER
Number of OSD languages	16
Plug and Play	✓

Power

Energy efficiency class (SDR) *	G
Energy consumption (SDR) per 1000 hours *	38 kWh

Performance

Low Blue Light technology	✔

Multimedia

Built-in speaker(s) *	✔
Number of speakers	2
RMS rated power	2 W
Built-in camera *	✘

Design

Market positioning *	Home
Product colour *	Black
Frameless design	✔
Front bezel colour	Black
Detachable stand	✔
Feet colour	Black

Power

Power consumption (typical) *	47 W
Power consumption (standby) *	0.3 W
Power consumption (off)	0.3 W
AC input voltage	100 - 240 V
AC input frequency	50/60 Hz
External power adapter	✘
Energy efficiency scale	A to G

Weight & dimensions

Weight (with stand)	6.8 kg

Packaging data

Stand included	✔
Cables included	HDMI
HDMI cable length	1.5 m
Quick start guide	✔
Package weight	8.68 kg
Package type	Box

4 038986 119900