

# QL-700

Plug and play  
PC connectable  
label printer

Free 3 year  
warranty  
as standard



**The QL-700 label printer makes printing labels easier and more affordable than ever before. Whether you're producing address labels, signage labels, ID passes or barcode labels, the QL-700 has the label type for you.**

Compact in size, but big in performance capability. Print up to 93 labels a minute, this easy to set-up printer offers hassle-free plug and print usage without the need for the installation of drivers or software.

For professional results every time, the in-built auto cutter professionally cuts bespoke sizes quickly when using the continuous roll, leaving you more time to design the ideal original label for the job. Or simply choose from the supplied suite of template designs for home or office applications.

## Key features:

- Unique continuous roll for printing labels up to 1m long
- Versatility due to a range of pre-sized labels and continuous rolls
- Durable in-built automatic cutter
- No need to install a driver, just plug it in your PC and print
- Print address labels directly from Microsoft Word, Excel and Outlook
- Space-saving design due to its small footprint
- Free P-touch Editor software for customisation of your labels.

## Pre-sized labels

DK Die-cut labels (white)	Labels per roll	Size (mm)	Item no.
Standard address label	400	29 x 90	DK-11201
Large address label	400	38 x 90	DK-11208
Small address label	800	29 x 62	DK-11209
Shipping label	300	62 x 100	DK-11202
File folder label	300	17 x 87	DK-11203
Multi-purpose label	400	17 x 54	DK-11204
Square label	1000	23 x 23	DK-11221
CD/DVD label (film)	100	58	DK-11207
Round label	1200	12	DK-11219
Round label	1000	24	DK-11218

## Continuous rolls

Width (mm)	DK continuous length	Length	Item no.
12	White paper	30.48m	DK-22214
29	White paper	30.48m	DK-22210
38	White paper	30.48m	DK-22225
50	White paper	30.48m	DK-22223
54	White paper (non-adhesive)	30.48m	DK-N55224
62	White paper	30.48m	DK-22205
62	White paper (removable)	30.48m	DK-44205
62	Yellow paper (removable)	30.48m	DK-44605
29	White film	15.24m	DK-22211
62	White film	15.24m	DK-22212
62	Yellow film	15.24m	DK-22606
62	Clear film	15.24m	DK-22113

<b>Included items</b>	
In the box	QL-700 printer Standard address die-cut labels (100 labels) 62mm wide continuous roll (62mm x 8 metres) USB cable AC power cord Documentation

<b>Printing / media</b>	
Printing technology	Direct thermal
Print resolution	300x300dpi (standard) / 300x600dpi (high resolution mode)
Print speed (single colour)*	Max 150mm/sec (93 labels/minute)
Label widths	12mm - 62mm
Maximum print width	60.96mm
Maximum print length	1 metre
Media sensor type	Reflective
Cutter	Yes (full cut / guillotine type)
Media types	DK rolls (DK die-cut labels / DK continuous tape)

<b>Connectivity</b>	
USB	USB version 2.0 full-speed (type mini-B connector)

<b>Memory</b>	
Flash (for label templates)	6MB

<b>Power</b>	
Power	Internal S/W power supply

<b>Weight / dimensions</b>	
Dimensions without carton	128(w) x 221(h) x 153(d) mm
Weight without carton	1.12kg

<b>Software / firmware</b>	
Operating system support (visit <a href="http://support.brother.com">http://support.brother.com</a> for latest downloads and support)	Microsoft® Windows Vista®/ Windows® 7 / Windows® 8 Windows® 8.1 / Windows® 10OS X v 10.10 / 10.11 / 10.12 Android 4.1 or higher
Barcode symbologies (using P-touch Editor)	CODE39, CODE128, UCC/EAN128(GS1-128), ITF(I-2/5), CODABAR(NW-7), UPC-A, UPC-E, EAN13, EAN8, ISBN-2(EAN13 AddOn2), ISBN-5(EAN13 AddOn5), Laser Barcode, POSTNET, RSS(RSS14 Standard, RSS14 Truncated, RSS14 Stacked, RSS14 Stacked Omni, RSS Limited, RSS Expanded, RSS Expanded Stacked), PDF417(Standard, Truncate, Micro), QR code(Model1, Model2, Micro), Data Matrix(ECC Square, ECC Rectangular), MaxiCode(Model2, Model3, Model4, Model5)RSS symbols / CODE93 / POSTNET / UPC/EAN EXTENSION / MSI / QR Code (model 1, model 2, micro QR)PDF417 (Standard, Truncate, MicroPDF417) / Data Matrix(ECC200 Square, ECC200 Rectangular) / MaxiCode / Aztec

\* Brother standard test environment